



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35156 SQ Shank Screwdr, 5/16 X 6" *Ideal*

Catalog Number	35156
Manufacturer	Ideal
Description	Ideal, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 5/16 In, Overall Length: 11 In, Shank Length: 6 In, Shank Shape: Square, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 5/16 In, Warranty: Lifetime Guarantee
Weight per unit	0.4167 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Type	Cushioned Rubber Grip
Shank Length	6
Shank Shape	Square
Tip Size	5/16
tip type	Keystone

Material, Color, and Finish

Blade Material	Chrome Vanadium Steel
----------------	-----------------------

Dimensions and Weight

Overall Length	11
----------------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	SQ SHANK SCREWDR, 5/16 X 6"
extra long description	IDEAL 35-156 SQ SHANK SCREWDR,5 16X
Features	The Heavy-Duty Square Shaft Keystone Cushioned-Grip Screwdriver features a tough, chrome vanadium steel blade and heavy-duty square shank that offers wrench-assisted turning. Its cushion-grip handle is resistant to oil, gas, and water, and helps to prevent slippage offering greater torque as well as superior comfort. Plate chipping is prevented by a vapor-blasted tip, which is also cross-ground to provide a precise and secure fit in the screw slot. The handle ends are also color-coded for quick and easy id
Long Description	IDEAL, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 5/16 IN, Overall Length: 11 IN, Shank Length: 6 IN, Shank Shape: Square, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 5/16 IN, Warranty: Lifetime Guarantee
Product Type	SQ Shank Screwdr, 5 16X6 In
Special Features	Features: Larger Shank For Heavy-Duty Applications; Identification Mark On Ends; Vapor-Blasted Tip Prevents Plate Chipping; Precision Ground Tip Provides Secure Fit In Screw Slot; Square-Shank Models Offer Wrench-Assisted Turning; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grips; Shank Size: 5/16 IN; Warranty: Lifetime Guarantee

Manufacturer Information

Brand	Ideal
GTIN	00783250351565
Manufacturers Part Number	35156
UPC	783250351565

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Heavy-Duty, Slotted, Keystone Tip

Packaging

Carton	1
Weight Per each	0.4167