



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35186 Cabinet Tip Screwdriver, 3/16" X 6" *Ideal*

Catalog Number	35186
Manufacturer	Ideal
Description	Ideal, Screwdriver, Electrician'S, Tip Size: 3/16 In, Overall Length: 9-3/4 In, Shank Length: 6 In, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Cabinet, Shank Size: 3/16 In
Weight per unit	0.2880 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Handle Type	Cushioned Rubber Grip
Shank Length	6
Tip Size	3/16
tip type	Cabinet

### Material, Color, and Finish

Blade Material	Chrome Vanadium Steel
----------------	-----------------------

### Dimensions and Weight

Overall Length	9-3/4
----------------	-------

### Descriptions

Description	CABINET TIP SCREWDRIVER, 3/16" X 6"
extra long description	IDEAL 35-186 Screwdriver ,Ideal,Elec
Features	These screwdrivers are made with nickel-chrome plating that is ideal for corrosion resistance. Plate chipping is prevented by a vapor-blasted tip. The screwdriver is 6-3/4-Inch long and features a tough, chrome vanadium steel round shank. The blade tip matches shank diameter for tough applications. Its cushion-grip handle is resistant to oil, gas and water and helps to prevent slippage for greater torque and superior comfort. It features a cross-ground tip to provide precise and secure fit in the screw slot
Long Description	IDEAL, Screwdriver, Electrician's, Tip Size: 3/16 IN, Overall Length: 9-3/4 IN, Shank Length: 6 IN, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Cabinet, Shank Size: 3/16 IN
Product Type	Screwdriver, Ideal, Electrician'S, 3/16 In Tip, 9-3/4 In Overall
Special Features	Features: Blade Tip Matches Shank Diameter; Vapor-Blasted Tip Prevents Plate Chipping; Cross-Ground Tip Provides Precise And Secure Fit In Screw Slot; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grip; Lifetime Guarantee; Identification Mark On Ends; Shank Size: 3/16 IN



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Ideal
GTIN	00783250351862
Manufacturers Part Number	35186
UPC	783250351862

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Electrician's

## Packaging

Carton	1
Weight Per each	0.288