



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35203 Number 2 Phillips Speed Driver

*Ideal*

|                  |                                       |
|------------------|---------------------------------------|
| Catalog Number   | 35203                                 |
| Manufacturer     | Ideal                                 |
| Description      | Ideal 35-203 Screwdriver, Ideal, Quic |
| Weight per unit  | 0.3500 (lbs/each)                     |
| Product Category | Pliers, Wrenches, Saw, Pouches        |

### Features

|              |                       |
|--------------|-----------------------|
| Handle Type  | Cushioned Rubber Grip |
| Shank Length | 6                     |
| Tip Size     | 3/16                  |
| tip type     | Phillips              |

### Material, Color, and Finish

|                |                       |
|----------------|-----------------------|
| Blade Material | Chrome Vanadium Steel |
|----------------|-----------------------|

### Dimensions and Weight

|                |       |
|----------------|-------|
| Overall Length | 9-3/4 |
|----------------|-------|

### Descriptions

|             |                                |
|-------------|--------------------------------|
| Description | NUMBER 2 PHILLIPS SPEED DRIVER |
|-------------|--------------------------------|

Features  
The Cabinet Quick Rotating Screwdriver is ideal for threading screws in switches, fixtures and anchors. For quick and easy use, it provides one-handed crank action. It has shank diameter that matches blade tip for tough applications and features a cross-ground tip to provide a precise and secure fit in the screw slot. Plate chipping is prevented by a vapor-blasted tip, and the screwdriver's nickel-chrome plating offers corrosion resistance and a smooth feel. The Cabinet Quick Rotating Screwdriver also feat

|                  |                                       |
|------------------|---------------------------------------|
| Long Description | IDEAL 35-203 Screwdriver, Ideal, Quic |
|------------------|---------------------------------------|

|              |  |
|--------------|--|
| Product Type | Screwdriver, Ideal, Quick-Rotating, PHL Head, 3/16 In Tip, 9-3/4 |
|--------------|--|

Special Features  
Features: Ideal For Threading Screws In Switches, Fixtures And Anchors; One-Handed Crank Action For Quick And Easy Use; Vapor-Blasted Tip Prevents Plate Chipping; Cross-Ground Tip Provides Precise And Secure Fit In Screw Slot; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grip; Lifetime Guarantee; Identification Mark On Ends; Shank Size: 3/16 IN



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250352036 |
| Manufacturers Part Number | 35-203         |
| UPC                       | 783250352036   |

## Taxonomies, Classifications, and Categories

|                      |                               |
|----------------------|-------------------------------|
| Category Description | HAND TOOLS                    |
| Type                 | Quick-Rotating, Phillips Head |

## Availability

|                     |          |
|---------------------|----------|
| Manufacturer Status | Inactive |
|---------------------|----------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.35 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | For Threading Screws In Switches, Fixtures And Anchors |
|-------------|--|