



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35688 21-In-1 Twist-A-Nut Screwdriver

*Ideal*

Catalog Number	35688
Manufacturer	Ideal
Description	Twist-A-Nut 21-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: #1 Phillips, #2 Phillips, #3 Phillips, 3/16 In Slotted, 1/4 In Slotted, 5/16 In Slotted, #1 Square, #2 Square, #15 Star, #20 Star, #25 Star, #30 Star, 3/32 In Hex, 1/8 In Hex, 3/16 In Hex, 5/32 In Hex, 1/4 In Nut, 5/16 In Nut and 7/16 In Nut
Weight per unit	0.8000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Handle Type	Textured, Ergonomic, Slip Resistant Comfort-Grip
-------------	--

### Material, Color, and Finish

Blade Material	Chrome Vanadium
Handle Material	SANTOPRENE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	21-IN-1 TWIST-A-NUT SCREWDRIVER
extra long description	IDEAL 35-688 Screwdriver, Ideal, Twis
Features	The Twist-a-Nut 21-in-1 Screwdriver is made of heavy-duty chrome vanadium shafts and provide robust strength for long life/professional use. The premium screwdriver ratchet mechanism can handle high torque without failure. The wire nut connector wrench reduces finger fatigue and gets in tight spots. It has an ergonomic, slip resistant, comfortable, textured grip to provide better torque. It resists perspiration, water, oil, chemicals and has Accu-Loop wire looping hole. It has size 1, size 2, size 3 tips
Long Description	Twist-a-Nut 21-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: #1 Phillips, #2 Phillips, #3 Phillips, 3/16 IN Slotted, 1/4 IN Slotted, 5/16 IN Slotted, #1 Square, #2 Square, #15 Star, #20 Star, #25 Star, #30 Star, 3/32 IN Hex, 1/8 IN Hex, 3/16 IN Hex, 5/32 IN Hex, 1/4 IN Nut, 5/16 IN Nut And 7/16 IN Nut
Product Type	Screwdriver, Ideal, Twist-A-Nut
Special Features	Wire-Nut connector wrench reduces finger fatigue and gets in tight spots; All metal ratchet, pro-quality, 28 tooth double action, twin-tooth ratchet; Premium screwdriver ratchet mechanism can handle high torque without failure; 225 LB of torque (stronger than human wrist can torque); Ergonomic, slip resistant comfort-grip; Heavy-duty chrome vanadium shafts provide robust strength and long life for professional use; Textured Santoprene grip provides excellent torque and resists perspiration, water, oil and

## Manufacturer Information

Brand	Ideal
GTIN	00783250716883
Manufacturers Part Number	35-688
UPC	783250716883

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	21-In-1 Screwdriver

## Packaging

Carton	1
Weight Per each	0.8