



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



370FG CRS-H 370FG 1 Wdgnut CST

Crouse-Hinds

Catalog Number	370FG
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 7 Wedge Nut Cover With Integral Gasket, Feraloy Iron Alloy, 1"
Weight per unit	0.5900 (lbs/each)
Product Category	Bodies & Covers

Features

Material	FERALOY IRON ALLOY
----------	--------------------

Dimensions and Weight

Height	6.97
Length	1.76
Width	0.84

Descriptions

Description	CRS-H 370FG 1 WDG NUT CST
extra long description	CRS-H 370FG 1 WDG NUT CST IRON FORM
Features	One hundred years after the introduction of the Condulet, Eaton remains the leader in conduit outlet bodies with its Crouse-Hinds series. The line has grown to six families manufactured in a variety of materials, and Form 7 bodies are offered in 11 different shapes to provide the most flexible offering on the market. Form 7 Condulet outlet bodies approach conduit in size for neat, compact installations. Many shapes and sizes are available for rigid threaded conduit. Our Form 7 family features an exclus
Long Description	Eaton Crouse-Hinds series Condulet Form 7 wedge nut cover with integral gasket, Feraloy iron alloy, 1"
Product Type	1 Wdgnut CST Iron Form 7 CVR/Gask
Special Features	With Neoprene Integral Gasket

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274233895
Manufacturers Part Number	370FG
UPC	782274233895

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Wedge nut cover with integral gasket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Weight Per each	0.59

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D