





Ordering Information for Box Sealing Tapes

Product Number	UPC (021200-)	Size	Inner Unit Pack	Case Qty.
Scotch® 3750 Premium Commercial Box Sealing Tape				
3750 Clear	06640*	48 mm x 50 m (1-4/5" x 54 yd.)	N/A	36 rolls
3750 Tan	72439	48 mm x 50 m (1-4/5" x 54 yd.)	1/pack	36 packs
3750 Clear	72441	48 mm x 50 m (1-4/5" x 54 yd.)	1/pack	36 packs
3750-DD (Clear)	06648*	With disposable dispenser: 1-4/5" x 54 yd. (48 mm x 50 m)	N/A	24 rolls
3750-DD (Tan)	06647*	With disposable dispenser: 1-4/5" x 54 yd. (48 mm x 50 m)	N/A	24 rolls
Scotch® 3732 and 3734 Printed Box Sealing Tape				
3732	72415*	1-4/5" x 109 yd. 48 mm x 100 m	bulk	36 rolls
3734	72417*	1-4/5" x 109 yd. 48 mm x 100 m	bulk	36 rolls
Highland™ 3710 Commercial Box Sealing Tape				
3710 Tan	14765	1-4/5" x 54 yd. (48 mm x 50 m)	bulk	36 rolls
3710 Tan	18814	1-4/5" x 109 yd. (48 mm x 100 m)	bulk	36 rolls
3710 Clear	14766	1-4/5" x 54 yd. (48 mm x 50 m)	bulk	36 rolls
3710 Clear	18813	1-4/5" x 109 yd. (48 mm x 100 m)	bulk	36 rolls
Scotch® H-122 Box Sealing Hand Dispensers				
H-122	06925	2" (50,8 mm)	1 each	8 dispensers
Highland 3770 Series Printed Box Sealing Tape				
3771 (red on white)	72301	1-9/10" x 104 yd. (48 mm x 100 m)	bulk	36 rolls
3772 (red on white)	72304	1-9/10" x 104 yd. (48 mm x 100 m)	bulk	36 rolls
3773 (red on white)	72307	1-9/10" x 104 yd. (48 mm x 100 m)	bulk	36 rolls
3774 (red on white)	72454	1-9/10" x 104 yd. (48 mm x 100 m)	bulk	36 rolls
3775 (red on white)	72458	1-9/10" x 104 yd. (48 mm x 100 m)	bulk	36 rolls
Highland 371 Industrial Box Sealing Tape				
371(Clear)	19279	2-4/5" x 54.6 yd. (72 mm x 50 mm)	bulk	24 rolls
371(Clear)	19280	2-4/5" x 109.3 yd. (72 mm x 100 mm)	bulk	24 rolls
371(Tan)	18197	2-4/5" x 54.6 yd. (72 mm x 50 mm)	bulk	24 rolls
371(Tan)	61525	2-4/5" x 109.3 yd. (72 mm x 100 mm)	bulk	24 rolls

*UPC prefix 051131.

Specifications for Filament Tapes

Product Number	Product Description	Tape Thickness	Temperature Rating	Typical Applications
 Scotch® 893 Industrial Grade Filament Tape	Industrial grade filament and packaging tape that is abrasion and moisture resistant.	6 mil	short term: 151°F (65°C)	High performance and long term adhesion for strapping and reinforcing
 Highland 897 Commercial Grade Filament Tape	Commercial grade filament tape with synthetic rubber resin adhesive.	6 mil	120°F (50°C)	General purpose, bundling and reinforcing
 Scotch® H-10 Filament Tape Dispensers	Filament Tape dispensers	N/A	N/A	Box sealing
 Scotch® H-180 Box Sealing Roll-on Dispensers	Box sealing Roll-on dispensers	N/A	N/A	Box sealing