

Power-Spade™ Spade Bits



- *The most innovative and fastest spade bit ever*
- *Smooth and effortless drilling*
- *Max operating speed 1500 RPM*
- *Available in a variety of sizes*
- *Offers less vibration than other bits*



Product Features



The Power-Spade™ Spade Bit offers industry-leading performance over any other style of spade bit on the market. Designed to meet the requirements of professional electricians, the Power-Spade is a giant leap forward in terms of speed, hole quality and ease of use. The patented*

full cone threaded tip increases drilling speed and reduces vibration while requiring less force to pull the bit through the material.

Full Cone Threaded Tip

FAST AND EFFORTLESS DRILLING

- 3x faster than the competition
- Self-feeding action
- Smoother drilling

Contoured Paddle

FAST CHIP REMOVAL

- Quickly removes material from hole
- Creates aggressive cutting blade angles for faster drilling

Spur and Reamer
FOR CLEANER HOLES


Hex Shank Power Groove
REDUCES SLIPPAGE



Fast, Powerful and Precise

Not only does the IDEAL Power-Spade perform faster and easier than other leading spade bits, its unique spur and reamer design also cuts cleaner entry and exit holes, with significantly reduced breakout splintering.

* Patent USD 604, 751S




Increased Drilling Speed with Less Force

3/4" SPADE BIT WITH CORDLESS DRILL


**Average Speed of 3 bits*

The Power-Spade™ features a unique full cone threaded tip, which increases both the speed and the ease of drilling over competitors' standard threaded tips. And the wave-like contour of the paddle improves chip removal over other spade bits. These features combine to require up to 50% less force to achieve even faster cuts than other leading competitors' spade bits.

Faster Drilling



Reduced Force



Product Listing



Power-Spade™ Spade Bits

All bits are 6" long and feature a 1/4" quick change hex shank.

Catalog Number	Description
36-403	3/4" x 4" Stubby
36-404	7/8" x 4" Stubby
36-405	1" x 4" Stubby
36-413	1/2"
36-415	5/8"
36-417	3/4"
36-419	7/8"
36-421	1"
36-422	1-1/8"
36-423	1-1/4"
36-432	4-pc. kit with pouch (5/8", 3/4", 7/8", 1")

4-Pc. Kit with Pouch

IDEAL has packaged the most commonly used Power-Spade bit sizes into a handy 4-piece kit in a sturdy canvas pouch.



36-432

4-piece kit with pouch (5/8", 3/4", 7/8", 1")

IDEAL INDUSTRIES, INC.

Becker Place, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA / Technical Hotline: 877-201-9005

International offices: Australia • Brazil • Canada • China • Germany • Mexico • Puerto Rico • UK

For complete sales office contact information, visit us at:

www.idealindustries.com