



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3LC28DB 8" 6W Led Under Counter Bar 24/30/40K Dark Bronze *American Lighting, Inc.*

|                  |   |
|------------------|---|
| Catalog Number   | 3LC28DB   |
| Manufacturer     | American Lighting, Inc.   |
| Description      | 3CT Dimmable 120V Uc, Uww+WW+WH, 6W, 8IN , DK BRZ, C/Etl/Us, 405LM, 2700-3000-4000K, 90+Cri |
| Weight per unit  | 0.8500 (lbs/each)   |
| Product Category | Led Undercabinet Lighting   |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 8" 6W LED UNDER COUNTER BAR 24/30/40K DARK BRONZE   |
| extra long description | 8 INCH LENGTH X 15/16 INCH DEPTH X 3-5/8 INCH HEIGHT SIZE; DARK BRONZE FINISH; ETL (CANADA AND US), FCC APPROVAL; UNDERCABINET, TASK LIGHTING APPLICATION; SURFACE MOUNT MOUNTING; UNDERCABINET LIGHT FIXTURE; DIMMABLE, LED LAMP TYPE; 6.5 WATT LAMP WATTAGE; 120 VOLT AC 60 HERTZ INPUT VOLTAGE; POWER COATED ALUMINUM HOUSING MATERIAL; 35000 LIFE IN HOUR; 335 LUMEN INTENSITY; INDOOR, DRY LOCATION AREA CLASSIFICATION; JA8 COMPLIANT; COLOR TEMPERATURE 2700/3000/4000 KELVIN; COLOR RENDERING INDEX 80 (2700 KELVIN), 9 |
| Long Description       | 3CT DIMMABLE 120V UC, UWW+WW+WH, 6W, 8IN , DK BRZ, C/ETL/US, 405LM,2700-3000-4000K, 90+CRI  |
| Product Type           | Led Undercabinet Light Fixture  |

### Manufacturer Information

|                           |                         |
|---------------------------|-------------------------|
| Brand                     | American Lighting, Inc. |
| GTIN                      | 00714176013657          |
| Manufacturers Part Number | 3LC2-8-DB               |
| UPC                       | 714176013657            |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING |
|----------------------|---|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.85 |