



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 44109 Wire Marker Booklet, Asst, 1-90, A-Z, +, -, /, 0 *Ideal*

Catalog Number	44109
Manufacturer	Ideal
Description	Ideal, Wire Marker Booklet, Size: 1/4 X 1-1/2 In Marker, Material: Plastic-Impregnated Cloth, Legend: 1-15, 16-90, A-Z, +, -, /, 0, Temperature Rating: -40 to 180 Deg F, Markers Per Page: 1-15 (6 Each), 16-90 (4 Each), A-Z (2 Each), +, -, /, 0 (2 Each), Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 Oz/In Width Ultimate, Includes: 450 Wire Markers and 450 Terminal Markers
Weight per unit	0.1400 (lbs/each)
Product Category	Markers & Marking Tapes

### Features

Legend	1-15, 16-90, A-Z, +, -, /, 0
Material	Plastic-Impregnated Cloth
Number of Pages	10/Booklet

### Material, Color, and Finish

Legend Color	Non-Smear Black
--------------	-----------------

### Dimensions and Weight

Size	1/4 X 1-1/2 IN Marker
------	-----------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	WIRE MARKER BOOKLET, ASST, 1-90, A-Z, +, -, /, 0
extra long description	IDEAL 44-109 Wire Marker Booklet,Id
Features	Convenient pocket-size bookletsPlastic, cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilPerforated 1/4 in. x 1-1/2 in. markers can be separated into half-length sizesNon-smear black legendSelf-sticking on wire and cableFor applications above or below groundTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate
Long Description	IDEAL, Wire Marker Booklet, Size: 1/4 X 1-1/2 IN Marker, Material: Plastic-Impregnated Cloth, Legend: 1-15, 16-90, A-Z, +, -, /, 0, Temperature Rating: -40 To 180 DEG F, Markers Per Page: 1-15 (6 Each), 16-90 (4 Each), A-Z (2 Each), +, -, /, 0 (2 Each), Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 OZ/IN Width Ultimate, Includes: 450 Wire Markers And 450 Terminal Markers
Product Type	Wire Marker Booklet, Ideal, SZ: 1/4 X 1-1/2 In MRKR, Plastic-Im
Special Features	Features: Convenient Pocket-Size Booklets; Plastic-Impregnated Cloth Construction For Long-Lasting Durability; Resists Abrasion, Moisture, Dirt And Oil; Perforated 1-1/2 IN Markers Can Be Separated Into Half-Length Sizes; Self-Sticking On Wire And Cable; Non-Smear Black Legend Ensures High Visibility; For Applications Above Or Below Ground; Ten Pages Per Booklet, 6 Markers Each 1-15, 4 Markers Each 16-90, 2 Markers Each A-Z, 2 Markers Each +, -, /, 0 ; Adhesion: 45 OZ/IN Width Ultimate; Includes: 450 Wire Mar

## Manufacturer Information

Brand	Ideal
GTIN	00783250441099
Manufacturers Part Number	44-109
UPC	783250441099

## Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
----------------------	----------------------------

## Packaging

Carton	5
Weight Per each	0.14

## Uses, Certifications, and Standards

standard	RoHS
Temperature Rating	-40 To 180