



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4412GRTNK 4X4X12 N3R Wireway R

Unity Manufacturing

Catalog Number	4412GRTNK
Manufacturer	Unity Manufacturing
Description	Wiring Trough, Code Gauge Low Carbon Steel Material; Gray Powder Coated Finish; 12 Inch; 12 Length In Inch; 4 Inch; 4 Width In Inch; 4 Inch; 4 Height In Inch; UL 870 Approval; Nema 3R Enclosure; Slip On Cover Type; Wiring Trough; No Knockout(S)
Weight per unit	4.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

### Features

Cover Type	Slip On
Item	WIRING TROUGH
Knockouts	NO
Material	CODE GAUGE LOW CARBON STEEL

### Material, Color, and Finish

Finish	Gray Powder Coated
--------	--------------------

### Dimensions and Weight

Height	4 INCH
Height in inch	4
Length	12 INCH
Length in inch	12
Width	4 INCH
Width in inch	4

### Descriptions

Commodity Description	NEMA TYPE 3R TROUGH & GUTTER
Description	4X4X12 N3R WIREWAY R
extra long description	LENGTH 12 INCH LENGTH; WIDTH 4 INCH; HEIGHT 4 INCH; NO KNOCKOUT(S); CODE GAUGE LOW CARBON STEEL MATERIAL; GRAY POWDER COATED FINISH; NEMA 3R ENCLOSURE; SLIP ON COVER; APPROVAL UL 870
Long Description	WIRING TROUGH, CODE GAUGE LOW CARBON STEEL MATERIAL; GRAY POWDER COATED FINISH; 12 INCH; 12 LENGTH IN INCH; 4 INCH; 4 WIDTH IN INCH; 4 INCH; 4 HEIGHT IN INCH; UL 870 APPROVAL; NEMA 3R ENCLOSURE; SLIP ON COVER TYPE; WIRING TROUGH; NO KNOCKOUT(S)
Product Type	Wiring Trough



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Unity Manufacturing
GTIN	00761515140604
Manufacturers Part Number	4412GRTNK
UPC	761515140604

## Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
----------------------	-------------------------------

## Packaging

Carton	1
Weight Per each	4

## Uses, Certifications, and Standards

Approval	UL 870
Enclosure	NEMA 3R