



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

277/480 VOLTS

44298 Voltage & Conduit Marker, "277/480V", Large, 1/Card

Ideal

| | |
|------------------|--|
| Catalog Number | 44298 |
| Manufacturer | Ideal |
| Description | Ideal, Marker Card, Voltage and Conduit, Large, Size: 2-1/4 In Width, Length: 9 In, Material: Vinyl-Impregnated Cloth, Legend: 277/480V, Temperature Range: -40 to 180 Deg F, Text Size: 1-3/4 In, Adhesion: 45 Oz/In Width Ultimate |
| Weight per unit | 0.1240 (lbs/each) |
| Product Category | Markers & Marking Tapes |

Features

| | |
|-------------------|-------------------------|
| Legend | 277/480V |
| Material | Vinyl-Impregnated Cloth |
| Number of Markers | 5 |

Dimensions and Weight

| | |
|--------|-------|
| Length | 9 |
| Width | 2-1/4 |

Descriptions

| | |
|------------------------|---|
| Description | VOLTAGE & CONDUIT MARKER,"277/480V", LARGE, 1/CARD |
| extra long description | IDEAL 44-298 Marker Card,Ideal,Volt |
| Features | Identify junction boxes, switches, circuit breakers, raceways, pipe and fuse boxesNon-conductive for user safetyHigh-adhesion properties with easy removabilityVinyl-impregnated cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilNon-smear, black legend on bright orange background for high visibilityTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate SELECT PART N |
| Long Description | IDEAL, Marker Card, Voltage And Conduit, Large, Size: 2-1/4 IN Width, Length: 9 IN, Material: Vinyl-Impregnated Cloth, Legend: 277/480V, Temperature Range: -40 to 180 DEG F, Text Size: 1-3/4 IN, Adhesion: 45 OZ/IN Width Ultimate |
| Product Type | Voltage & Conduit Marker, "277/480V", Large, 1/Card |
| Special Features | Adhesion: 45 OZ/IN Width Ultimate;Features: Identify Junction Boxes, Switches, Circuit Breakers,Raceways, Pipe And Fuse Boxes;High-Adhesion Properties With Easy Removability;Non-Conductive For User Safety;Non-Smear, Black Legend On Bright Orange BackgroundFor High Visibility;Resist Abrasion, Moisture, Dirt And Oil;Temperature Range: -40 DEGF To 180 DEGF (-40 DEGC To 82 DEGC) Adhesion: 45 Oz/IN Width Ultimate;Temperature Range: -40 to 180 DEG F;Text Size: 1-3/4 IN;Vinyl-Impregnated Cloth Construction Provid |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250442980 |
| Manufacturers Part Number | 44-298 |
| UPC | 783250442980 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
| Type | Voltage And Conduit, Large |

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Weight Per each | 0.124 |

Uses, Certifications, and Standards

| | |
|----------|------|
| standard | RoHS |
|----------|------|