



Catalog Number: 4436-GSC3R-NK  
Item Description: N3R SCREW CVR GUTTER NK  
UPC Code: 784572106499


Brand Name: Milbank  
Type: Wiring Trough  
Special Features: Key Locking Cylinder Latch Provision,  
Sealing Eye Lance  
Application: Wireway  
Standard: UL Listed, Type 3R  
Cover Type: Screw Cover  
Enclosure: Outdoor Enclosure  
Nominal Cross Section: 4x4  
Straight Section Length: 36  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False





*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CAT. NO.	U/L LABEL
4436-GSC3R	1002943
RC-4436-GSC3R	1125051
SPRSCG-4436	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	1153003	BACK WELDMENT
2	1	1004405	FRONT
3	3	1001290	SCREW, 10-32 X 5/16
4	1	1002898	LABEL, RATING 4x4 GSC3R
5	1	(SEE CHART)	UL LABEL, WIREWAY
6	1	1003085	PAD (NOT SHOWN)



Material:		16 GA. GALV. STEEL		 General Offices: Kansas City, MO		
Shear/ Die#:						
Finish:		MILBANK LIGHT GRAY		Title: SCREW COVER WIREWAY NEMA TYPE 3R		
Part Wt.:				Catalog No.: (SEE CHART)		
Tolerances:		Third Angle		Customer:		
Unless Specified Otherwise				Drawing No.: 270		
X.X ±.1				Date: 5/6/11		
X.XX ±.03				Sheet 1 of 1		
X.XXX ±.015						
X* ±2*						
Scale: NTS		Checked By:				
Drawn By: D.F.		Approved By:				
REV.	DATE	DESCRIPTION	BY			
B	5/6/11	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN; 1004405 WAS 1010725 (ECO #20576)	D.F.			
C	8/12/11	ADD #1003085 PAD WITH SLIT (mECO#21106)	JLT			



Catalog Number: 4436-GSC3R-NK  
Item Description: N3R SCREW CVR GUTTER NK  
UPC Code: 784572106499


Brand Name: Milbank  
Type: Wiring Trough  
Special Features: Key Locking Cylinder Latch Provision,  
Sealing Eye Lance  
Application: Wireway  
Standard: UL Listed, Type 3R  
Cover Type: Screw Cover  
Enclosure: Outdoor Enclosure  
Nominal Cross Section: 4x4  
Straight Section Length: 36  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CAT. NO.	U/L LABEL
4436-GSC3R	1002943
RC-4436-GSC3R	1125051
SPRSCG-4436	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	1153003	BACK WELDMENT
2	1	1004405	FRONT
3	3	1001290	SCREW, 10-32 X 5/16
4	1	1002898	LABEL, RATING 4x4 GSC3R
5	1	(SEE CHART)	UL LABEL, WIREWAY
6	1	1003085	PAD (NOT SHOWN)



Material:	16 GA. GALV. STEEL	 <p>General Offices: Kansas City, MO</p>									
Shear/ Die#:											
Finish:	MILBANK LIGHT GRAY										
Part Wt.:											
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2*		Title: SCREW COVER WIREWAY NEMA TYPE 3R Catalog No.: (SEE CHART) Customer: Drawing No.: 270									
REV.	DATE	DESCRIPTION	BY	Scale:	NTS	Checked By:		Date:	5/6/11	Sheet	1 of 1
B	5/6/11	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN; 1004405 WAS 1010725 (ECO #20576)	D.F.	Drawn By:	D.F.	Approved By:					
C	8/12/11	ADD #1003085 PAD WITH SLIT (mECO#21106)	JLT								