



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 444RTSC 4X4X4 RT Junction Box *Unity MFG*

Catalog Number	444RTSC
Manufacturer	Unity MFG
Description	Screw Cover, Low Carbon Steel, Light Gray Powder Coated, 4 In Overall Depth, 4 In Overall Length, 4 In Overall Width, 1 LB
Weight per unit	1.0 (lbs/each)
Product Category	Enclosure General Accessories

### Features

Cable Entry	(1) (1/2 - 3/4 IN) Conduit Concentric Knockout Bottom, (1) (3/4 - 1 IN) Conduit Concentric Knockout Bottom V-Notch Pattern
connection	Screw Terminal
Knockouts	Yes

### Material, Color, and Finish

Color	Gray
-------	------

### Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel, Drip Shield Top, Seam Free Sides
Description	4X4X4 RT JUNCTION BOX
extra long description	UNT 444RTSC N3R SCREW COVER PULL BO
Special Features	Enclosure and cover are fabricated from code gauge galvanized steel for painted steel; Enclosure body has embossed mounting holes on the back; Cover is held secure by sliding it under the top end flange and fastening it with plated screws on the bottom end flange, (larger sizes use two studs and wing nuts); Thermoset polyester powder coated over phosphatized surface finish; Slip-on cover without gasket; (2) bottom knockouts; For use as wiring and junction boxes

### Manufacturer Information

Brand	Unity
GTIN	00761515340103
Manufacturers Part Number	444RTSC
UPC	761515340103

### Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Screw-On Slip-On Cover Enclosure

### Packaging

Carton	1
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Mounting  
standard

WALL

C/US UL 50 And UL 50E - Type 3R: Intended For Indoor Use  
Primarily To Provide A Degree Of Protection Against Rain, Sleet,  
Damage From External Ice Formation, CSA C22.2 No. 40 Certified,  
IEC 60529, RoHS Compliant