



Catalog Number: 4460-GHC1-NK
Item Description: N1 HINGE CVR GUTTER NK
UPC Code: 784572106635


Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Hinge Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 4x4
Straight Section Length: 60
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False





Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG# | LABEL# |
|-----------------|---------|
| 4460-GHC1(-) | 1002943 |
| RC-4460-GHC1(-) | 1125051 |
| SPH-445 | 1132575 |

| NO. | QTY. | PART NO. | DESCRIPTION |
|-----|------|-------------|------------------------|
| 1 | 1 | (SEE CHART) | BACK |
| 2 | 1 | (SEE CHART) | TOP |
| 3 | 5 | 1003198 | HINGE |
| 4 | 7 | 1001290 | SCREW, 10-32 X 5/16 |
| 5 | 1 | (SEE CHART) | LABEL (U/L LISTING) |
| 6 | 1 | 1002900 | LABEL, WIREWAY FITTING |
| 7 | 3 | 1002880 | BAG ASSY. |



| SUFFIX | BACK # | COVER # |
|--------|---------|---------|
| -SU | 1105200 | 1002281 |
| -SUC | 1128809 | 1118926 |
| -SO | 1128810 | 1128772 |
| -SUNK | 1110151 | 1002281 |
| -NK | 1128811 | 1128772 |
| -SUNKC | 1128812 | 1118926 |



| SUFFIX | FINISH |
|--------|-------------|
| NONE | PAINTED |
| -NP | NOT PAINTED |

NOTE:
1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)

| | | |
|--|--------------------|--|
| Material: | 16 GA. - SEE CHART | General Offices: Kansas City, MO |
| Shear/ Die#: | | |
| Finish: | SEE CHART | Title: HINGE COVER WIREWAY 4 x 4 x 60, TYPE 1 NEMA ENCLOSURE |
| Part Wt.: | | Catalog No.: (SEE CHART) |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2" | | Customer: MILBANK STANDARD |
| Third Angle | | Drawing No.: 355-11 |
| Scale: | NTS | Date: 05/09/02 |
| Drawn By: | DY | Sheet 1 of 1 |
| Checked By: | | |
| Approved By: | | |

| REV | DATE | DESCRIPTION | BY | DL |
|-----|---------|---|-----|----|
| D | 8-27-07 | ADDED BACK & COVER CHART & IT. 1001290 QTY. W 10 ECO. 15946 | | |
| D1 | 4/9/08 | ADDED CHART & REMOVED NOTE #2 (ECO.17139) | JLT | |



Catalog Number: 4460-GHC1-NK
Item Description: N1 HINGE CVR GUTTER NK
UPC Code: 784572106635


Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Hinge Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 4x4
Straight Section Length: 60
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False





Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG# | LABEL# |
|-----------------|---------|
| 4460-GHC1(-) | 1002943 |
| RC-4460-GHC1(-) | 1125051 |
| SPH-445 | 1132575 |

| NO. | QTY. | PART NO. | DESCRIPTION |
|-----|------|-------------|------------------------|
| 1 | 1 | (SEE CHART) | BACK |
| 2 | 1 | (SEE CHART) | TOP |
| 3 | 5 | 1003198 | HINGE |
| 4 | 7 | 1001290 | SCREW, 10-32 X 5/16 |
| 5 | 1 | (SEE CHART) | LABEL (U/L LISTING) |
| 6 | 1 | 1002900 | LABEL, WIREWAY FITTING |
| 7 | 3 | 1002880 | BAG ASSY. |



| SUFFIX | BACK # | COVER # |
|--------|---------|---------|
| -SU | 1105200 | 1002281 |
| -SUC | 1128809 | 1118926 |
| -SO | 1128810 | 1128772 |
| -SUNK | 1110151 | 1002281 |
| -NK | 1128811 | 1128772 |
| -SUNKC | 1128812 | 1118926 |



| SUFFIX | FINISH |
|--------|-------------|
| NONE | PAINTED |
| -NP | NOT PAINTED |

NOTE:
1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)

| | | |
|--|--------------------|--|
| Material: | 16 GA. - SEE CHART | General Offices: Kansas City, MO |
| Shear/ Die#: | | |
| Finish: | SEE CHART | Title: HINGE COVER WIREWAY 4 x 4 x 60, TYPE 1 NEMA ENCLOSURE |
| Part Wt.: | | Catalog No.: (SEE CHART) |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2" | | Customer: MILBANK STANDARD |
| Third Angle | | Drawing No.: 355-11 |
| Scale: | NTS | Date: 05/09/02 |
| Drawn By: | DY | Sheet 1 of 1 |
| Checked By: | | |
| Approved By: | | |

| REV | DATE | DESCRIPTION | BY | DL |
|-----|---------|---|-----|----|
| D | 8-27-07 | ADDED BACK & COVER CHART & IT. 1001290 QTY. W 10 ECO. 15946 | | |
| D1 | 4/9/08 | ADDED CHART & REMOVED NOTE #2 (ECO.17139) | JLT | |