



M18 REDLITHIUM™

THE WORLD'S FIRST & ONLY 18V HIGH DEMAND™ 9.0 BATTERY

[Learn More](#)

Swap Banner



6" 18 TPI Thin Kerf Ice Hardened™ SAWZALL® Blades (5 Pk)

48-00-4184



What's Included

(1) 6" 18 TPI Thin Kerf Ice Hardened™ SAWZALL® Blades (5 Pk) (48-00-4184)

Where to Buy

- Shop Online
- Find Local

Features

- Optimized tooth design providing 2X more life than our previous generation SAWZALL® blades
- Tough Neck™ ribs strengthen the blade tang and minimize breakage
- Grid Iron™ honeycomb pattern increases blade rigidity to resist blade buckling.

Specifications

TPI	18
Length	6.06"
Profile	Thin Kerf
Pack Qty	5 Pack
Shank	1/2" Universal
Material	Scheduled 80 Pipe Strut

Overview

Thin Kerf metal-cutting blades with the Double Duty Upgrade™ feature a tooth form that is optimized for the longest life and increased speed. Tough Neck™ is engineered to protect against tang breakage and delivers the strongest SAWZALL® blade tang on the market. Ice Hardened blades are cryogenically treated for up to 50% longer life. Maintaining a short profile and thin body, these blades are ideal for making fast, flexible cuts.

Model Options

Item/Cat #	TPI	Length	Profile	Pack Qty
------------	-----	--------	---------	----------

48-01-8182	14	6.06"	Thin Kerf	50 Pack	Shop Online Find Local
48-00-4187	14	9.09"	Thin Kerf	5 Pack	Shop Online Find Local
48-01-8187	14	9.09"	Thin Kerf	50 Pack	Shop Online Find Local
48-00-4182	14	6.06"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-4184	18	6.06"	Thin Kerf	5 Pack	Shop Online Find Local
48-01-9188	18	9.09"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-00-4186	24	6.06"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-4189	18	95.12"	Thin Kerf	5 Pack	Shop Online Find Local
48-00-4188	18	9.09"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-6092	10	6.06"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-8184	18	6.06"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-8186	24	6.06"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-8188	18	9.09"	Thin Kerf	50 Pack	Shop Online Find Local
48-01-9182	14	6.06"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-9184	18	6.06"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-9186	24	6.06"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local
48-01-9187	14	9.09"	Thin Kerf	100 Pack (Bulk)	Shop Online Find Local