



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48138375 3/4 X 72" Flexible Cable Auger Bit

Milwaukee Electric Tool

Catalog Number	48138375
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® 3/4" X 72" Flexible Cable Auger Bit Provides Flexible Drilling and Clean Holes When Installing Small Wire Systems In Unreachable Spaces. The Screw Tip Design Allows For Faster Wood Boring. The Dual Pull-Through Hole Design Features Holes On Both Ends For Feeding Wire Through Drilled Holes. The Auger Style Flute Allows For Faster Drilling and Easy Chip Ejection. The Flexible Shaft Allows You to Drill Inside Walls or Between Floors With Greater Precision and Ease When Installing All Types Of S
Weight per unit	1.8 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Flute Length	68.0
Number of Flutes	2
Shank Diameter	0.375

Dimensions and Weight

Overall Length	72.0
----------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/4 X 72" FLEXIBLE CABLE AUGER BIT
extra long description	MILW 48-13-8375 FLEX BIT 3/4 X 72"
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	The MILWAUKEE® 3/4" x 72" Flexible Cable Auger Bit provides flexible drilling and clean holes when installing small wire systems in unreachable spaces. The screw tip design allows for faster wood boring. The dual pull-through hole design features holes on both ends for feeding wire through drilled holes. The auger style flute allows for faster drilling and easy chip ejection. The flexible shaft allows you to drill inside walls or between floors with greater precision and ease when installing all types of S
Product Type	Flex Bit 3/4 X 72"
Short Description	FLEX Bt 3/4x72"
Special Features	3/4 IN Diameter, 72 IN Overall Length; For Installers Of Small Wire Systems; Flexible Steel Shaft Bits Let You Reach Unreachable Areas Behind Walls With Greater Ease And Precision; Placement Guide Tool 48-08-0275 For Setting Bit Into Proper Drilling Location Within The Interior Of Walls

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242094806
Manufacturers Part Number	48-13-8375
UPC	045242094806

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	bit cable

Packaging

Carton	1
Package	12
Weight Per each	1.76



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application For Installers of Small wire cable or wiring systems.....