



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48221025M 25' Magnetic Tape Measure

*Milwaukee Electric Tool*

MAGNETIC C:

Catalog Number	48221025M
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® 25FT Magnetic Tape Measure Delivers A Straighter, Stiffer Blade. The Blade Remains Stiff At 12', Resulting In Less Blade Rollover and Allowing For Efficient Measuring Of Common Jobsite Materials. This Tape Measure Feels Balanced In The Hand For More Control Of The Body and Blade. The Low-Profile Magnet Delivers Improved Top and Bottom Hook Grab. The Blade Retracts Smoothly and Features A Double-Sided Anti-Tear Coating That Reinforces The First 6". The Tape Delivers 15' Of Reach and 12' Of ST
Weight per unit	1.2 (lbs/each)
Product Category	Tools & Testers

### Features

Accuracy	+/- 1/16 in
Belt Clip	Yes
Tape Length	25

### Material, Color, and Finish

Blade Material	Steel
Case Material	ABS Plastic

### Dimensions and Weight

Width	1.18
-------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	25' MAGNETIC TAPE MEASURE
extra long description	MILW 48-22-1025M 25' Magnetic Tape
Features	MILWAUKEE® is committed to continuously innovating Layout Hand Tools. With a full line of Tape Measures, MILWAUKEE® provides a solution for every user, ranging from reach, to durability, to compact size. STUD™ is the most durable Tape Measure in the industry with the longest lasting blade, combating blade tear. Wide Blade Tapes deliver the longest reach & straightest standout, allowing just one user to easily and accurately make long distance measurements. In addition to Tape Measures, Milwaukee provides a
Long Description	The MILWAUKEE® 25ft Magnetic Tape Measure delivers a Straighter, Stiffer Blade. The blade remains stiff at 12', resulting in less blade rollover and allowing for efficient measuring of common jobsite materials. This tape measure feels balanced in the hand for more control of the body and blade. The low-profile magnet delivers improved top and bottom hook grab. The blade retracts smoothly and features a double-sided anti-tear coating that reinforces the first 6". The tape delivers 15' of Reach and 12' of St
Product Type	25' Magnetic Tape

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242822676
Manufacturers Part Number	48-22-1025M
UPC	045242822676

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
----------------------	------------

## Packaging

Carton	6
Package	24
Weight Per each	1.232