



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48271371 Flat Boring Bit 1-3/8" X 6"

Milwaukee Electric Tool

Catalog Number	48271371
Manufacturer	Milwaukee Electric Tool
Description	For Fast, Small Hole Drilling In Wood, Count On Milwaukee'S Premium Quality 1-3/8 In. Flat Boring Bit. Made Of Heat Treated High Carbon Steel, The Flat Boring Bit Bores Clean Holes At Any Angle In Wood, Plastic, Plywood and Formica. The Drill Point and Cutting Edges Can Be Resharpended Often For Economical Hole Drilling. Bit Offers A 6 In. Drilling Depth But Can Be Used With 12 In. Extension, 48-28-3350, For Extended Deep Hole Drilling. One Per Package.
Weight per unit	0.1450 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Flute Length	5
Material	Heat-Treated High-Carbon Steel
Shank Diameter	0.25

Dimensions and Weight

Length	6
Overall Length	6-3/8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	FLAT BORING BIT 1-3/8" X 6"
extra long description	MILW 48-27-1371 Flat Boring Bit
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	For fast, small hole drilling in wood, count on Milwaukee's premium quality 1-3/8 in. flat boring bit. Made of heat treated high carbon steel, the flat boring bit bores clean holes at any angle in wood, plastic, plywood and Formica. The drill point and cutting edges can be resharpened often for economical hole drilling. Bit offers a 6 in. drilling depth but can be used with 12 in. extension, 48-28-3350, for extended deep hole drilling. One per package.
Product Type	Flat Boring Bit
Short Description	Flat Boring Bt
Special Features	1-3/8 IN Bit Diameter; 1/4 IN Shank Diameter; 6-3/8 IN Overall Length; Drill Point And Cutting Edges Can Be Resharpened

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242121359
Manufacturers Part Number	48-27-1371
UPC	045242121359

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	STUBBY

Packaging

Carton	1
Package	150
Weight Per each	0.145

Uses, Certifications, and Standards

Application	For Bores Clean Holes At Any Angle In Wood, Plastic, Plywood And Formica
-------------	--