



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892742 5/8" S&D Black Oxide Drill Bit

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 48892742 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Milwaukee'S Thunderbolt® Silver & Deming Drill Bits Are Designed For Performance In Low to High Tensile Strength Materials, Stainless Steel and Cast Iron. Thunderbolt® Twist Drill Bits Are Made From Premium Industrial-Grade Steel With Heavy-Duty Cutting Surfaces That Power Through Deep or Shallow Holes With Lightning Speed. A Special Flute Geometry Adds Strength While Providing Increased Chip Ejection. Thunderbolt® Twist Drill Bits Have A Heavy Duty 135 Degree Split Point For Easy Penetration and A 1/2 In. |
| Weight per unit | 0.3300 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|------------------|------------|
| Drill Diameter | 0.625 |
| Flute Length | 4.0 |
| Grade | Heavy Duty |
| package quantity | 1 |
| Shank Diameter | 0.25 |

Dimensions and Weight

| | |
|--------|-----|
| Length | 6.0 |
|--------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 5/8" S&D BLACK OXIDE DRILL BIT |
| extra long description | MILW 48-89-2742 5/8" S&D Black Oxid |
| Features | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening, |
| Long Description | Milwaukee's Thunderbolt® Silver & Deming drill bits are designed for performance in low to high tensile strength materials, stainless steel and cast iron. Thunderbolt® twist drill bits are made from premium industrial-grade steel with heavy-duty cutting surfaces that power through deep or shallow holes with lightning speed. A special flute geometry adds strength while providing increased chip ejection. Thunderbolt® twist drill bits have a heavy duty 135 degree split point for easy penetration and a 1/2 in. |
| Product Type | 5/8" S&D Black Oxide Bit |

Manufacturer Information

| | |
|---------------------------|---------------------------------------|
| Brand | Milwaukee® |
| GTIN | 00045242167166 |
| Manufacturers Part Number | 48-89-2742 |
| series | Milwaukee® S&D Black Oxide drill bits |
| UPC | 045242167166 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
|----------------------|-----------------------------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 75 |
| Weight | 0.325 |
| Weight Per each | 0.33 |