



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48899249 Shockwave Imp Duty #9 7/8"/1-1/8" *Milwaukee Electric Tool*

Catalog Number	48899249
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee®'S Shockwave™ Impact Duty™ Step Bits Are Engineered to Deliver The Most Durable and Fastest Holes In The Market. Made In The Usa With Global Materials, These Step Bits Have Best-In-Class Performance In Impact Drivers and The Versatility to Be Used In Drills. The 1/4 In. Hex Shank With An Optimized Shockzone™ Provide The Industry'S Most Durable Shank, Reducing Early Shank Breaks. A Titanium Aluminum Nitride (Tibone) Coating Helps Deliver 5X Longer Life, While The Rapid Strike™ Tip and Dual Spiral
Weight per unit	0.3300 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Flute Length	2.13
Shank Diameter	0.25

### Dimensions and Weight

Length	3.765
--------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	SHOCKWAVE IMP DUTY #9 7/8"/1-1/8"
extra long description	MILW 48-89-9249 Step Bit #9 7/8 in.
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee®'s SHOCKWAVE™ Impact Duty™ step bits are engineered to deliver the most durable and fastest holes in the market. Made in the USA with global materials, these step bits have best-in-class performance in impact drivers and the versatility to be used in drills. The 1/4 in. hex shank with an optimized Shockzone™ provide the industry's most durable shank, reducing early shank breaks. A titanium aluminum nitride (TiBone) coating helps deliver 5x longer life, while the Rapid Strike™ tip and dual spiral
Product Type	Step Bit #9 7/8 In. & 1-1/8 In.
Short Description	Step Bit #9 7/8 " & 1-1/8 "

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242505104
Manufacturers Part Number	48-89-9249
UPC	045242505104

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

## Packaging

Carton	1
Weight Per each	0.33