



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48899284 #4 Cobalt Step Drill Bit

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 48899284 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee® #4 Cobalt Step Drill Bits Are Engineered to Deliver Up to 15X The Life In Stainless Compared to Current Solutions and Up to 1000 Holes In Mild Steel. The Cobalt Step Drill Bits Are Recommended Up to 14GA. The Elongated Dual-Flute Design Also Offers The Best Heat Management Combined With The Smaller Steps For Smoothest Drilling Experience and A Rapid Strike™ Tip That Allows For 2X Faster Starts In Stainless. Made In The Usa With Global Materials, These Step Bits Have Best-In-Class Performance |
| Weight per unit | 0.2300 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|----------------|-------|
| Flute Length | 2.78 |
| Shank Diameter | 0.375 |

Dimensions and Weight

| | |
|--------|------|
| Length | 3.65 |
|--------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | #4 COBALT STEP DRILL BIT |
| extra long description | MILW 48-89-9284 Milwaukee Cobalt St |
| Features | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening, |
| Long Description | The MILWAUKEE® #4 Cobalt Step Drill Bits are engineered to deliver up to 15X the life in stainless compared to current solutions and up to 1000 holes in mild steel. The Cobalt Step Drill Bits are recommended up to 14ga. The elongated dual-flute design also offers the best heat management combined with the smaller steps for smoothest drilling experience and a Rapid Strike™ tip that allows for 2X faster starts in stainless. Made in the USA with global materials, these step bits have best-in-class performance |
| Product Type | Milwaukee Cobalt Step Drill Bit #4 |
| Short Description | Cobalt Step Drill Bt #4 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242567614 |
| Manufacturers Part Number | 48-89-9284 |
| UPC | 045242567614 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
|----------------------|-----------------------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.23 |