



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



49251233 Open-Lok Ti CHRGD Bi-Met Blades 3PK *Milwaukee Electric Tool*

| | |
|------------------|---|
| Catalog Number | 49251233 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee® Open-Lok™ 1-3/8" Titanium Charged™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades Are Made From Premium High-Speed Steel. These Bi-Metal Blades Are Ideal For Cuts In Wood, Nails, PVC, and Drywall. Titanium Charged™ Bi-Metal Blades Have An Optimized Titanium Blend For Maximum Wear-Resistance and Up to 15X Longer Life VS. High Carbon Steel (HCS) Blades. These Blades Feature A Reinforced Universal Fit Open-Lok™ Anchor For Better Strength & Control and Allow For Quick Blade Changes Across |
| Weight per unit | 0.1900 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|-----------------|------------|
| Blade Thickness | 0.025 |
| blade type | Multi-Tool |

Material, Color, and Finish

| | |
|----------------|-------------------|
| Blade Material | High Carbon Steel |
|----------------|-------------------|

Dimensions and Weight

| | |
|------|-------|
| Size | 1-3/8 |
|------|-------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | OPEN-LOK TI CHRGD BI-MET BLADES 3PK |
| extra long description | MILW 49-25-1233 1-3/8" TITANIUM BI- |
| Features | MILWAUKEE® Oscillating Multi-Tool Accessories provide a complete solution for cutting, scraping, sanding and grinding across a wide range of materials and applications. Equipped with an OPEN-LOK™ Universal blade anchor for quick blade changes. Made with high quality materials and advanced manufacturing processes to deliver professional grade performance and market leading innovation. |
| Long Description | The MILWAUKEE® OPEN-LOK™ 1-3/8" TITANIUM CHARGED™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades are made from premium high-speed steel. These bi-metal blades are ideal for cuts in wood, nails, PVC, and drywall. TITANIUM CHARGED™ Bi-Metal blades have an optimized titanium blend for maximum wear-resistance and up to 15x longer life vs. high carbon steel (HCS) blades. These blades feature a reinforced Universal Fit OPEN-LOK™ anchor for better strength & control and allow for quick blade changes across |
| Product Type | 1-3/8" Titanium Bi-Metal Blades 3PK |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242570973 |
| Manufacturers Part Number | 49-25-1233 |
| UPC | 045242570973 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
| Type | Multi-Tool Blades |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 0.19 |

Uses, Certifications, and Standards

| | |
|-------------|----------------|
| Application | Multi-Material |
|-------------|----------------|