



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **49240146 M12 Work Light** *Milwaukee Electric Tool*

|                  |   |
|------------------|---|
| Catalog Number   | 49240146  |
| Manufacturer     | Milwaukee Electric Tool   |
| Description      | The M12™ Cordless Led Work Light Outlasts and Outperforms All Other Subcompact Lights. Powered By An M12™ Red Lithium™ Battery, The Work Light Is 2X Brighter and Whiter Than Conventional Incandescent Bulbs and Runs Up to Twice As Long. With A Sealed Aluminum Head to Provide Impact and Weather Resistance, Milwaukee® Provides A Limited Lifetime Led Warranty. A Magnetic Back Allows Hands-Free Use While A 90 Degree Rotating Head Allows The User to Easily Point The Light Beam At The Desired Work Area. |
| Weight per unit  | 0.7400 (lbs/each)   |
| Product Category | Worklight Lighting  |

### **Features**

|                 |                 |
|-----------------|-----------------|
| battery         | Lithium-Ion     |
| Battery Size    | Battery Packs   |
| Battery Voltage | 12              |
| bulb type       | LED             |
| charge time     | 0.5             |
| lumens          | 160             |
| Material        | Rugged Overmold |
| Voltage Rating  | 12              |
| Water Resistant | NO              |

### **Material, Color, and Finish**

|                   |      |
|-------------------|------|
| color temperature | 5600 |
|-------------------|------|

### **Dimensions and Weight**

|      |                 |
|------|-----------------|
| Size | 8.500 IN Length |
|------|-----------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | M12 WORK LIGHT  |
| extra long description | MILW 49-24-0146 12V LED WORKLIGHT   |
| Features               | M12™ Cordless LED Work Light  |
| Long Description       | The M12™ cordless LED work light outlasts and outperforms all other subcompact lights. Powered by an M12™ Red Lithium™ battery, the work light is 2X brighter and whiter than conventional incandescent bulbs and runs up to twice as long. With a sealed aluminum head to provide impact and weather resistance, Milwaukee® provides a limited lifetime LED warranty. A magnetic back allows hands-free use while a 90 degree rotating head allows the user to easily point the light beam at the desired work area. |
| Product Type           | 12V Led Worklight   |
| Short Description      | 12V LED WORKLIGHT   |
| Special Features       | Features: Aluminum Head Impact And Weather Resistant; 90 DEG Rotating Head Aims Light At Work Space; Magnetic Back Hands-Free Use; M12 Works With Milwaukee 12 V Redlithium Battery Pack; Tool Weight: 0.900 LB   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Milwaukee®     |
| GTIN                      | 00045242188604 |
| Manufacturers Part Number | 49-24-0146     |
| UPC                       | 045242188604   |

## Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | FLASHLIGHTS AND BATTERIES |
| Type                 | Cordless, LED             |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.74 |