



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 East 4th Street  
79720-0000, TX Big Spring  
Phone: 432-264-0316  
Fax: 432-264-0483



## 4DTN224ZN BLTD Dovetail Nut

Cooper B-Line/Cable Tray

Catalog Number	4DTN224ZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series 4DIMENSION Strut Channel Nuts, Installs With Quarter Turn, Steel, Safety Factor 3.0, Dove-Tail Combo Nut Washer, Electro-Plated Zinc, 400 LBS Pull Out Strength, 300 LBS Slip Strength, 3/8"-16 Thread Size
Weight per unit	0.0440 (lbs/each)
Product Category	Channel & Strut Fittings

### Material, Color, and Finish

Color	DURA GREEN
Finish	Zinc Plated

### Dimensions and Weight

Height	0.259 IN
Size	1.26 IN X 0.827 IN X 0.259 IN
Width	0.827 IN

### Descriptions

Also Known As...	Boingie Nut Spring Nut (Strut)
Description	BLTD DOVETAIL NUT
extra long description	B-LINE 4DTN224ZN 4D DOVETAIL TWIRL-
Features	The unique design of the 4Dimension strut channel nuts can be used on multiple sides of the 4Dimension strut channel, allowing for numerous designs and applications. The 4Dimension wire wing nut and the slide-In nuts can also be used with traditional strut.
Long Description	Eaton B-Line series 4Dimension strut Channel nuts, Installs with quarter turn, Steel, Safety Factor 3.0, Dove-tail combo nut washer, Electro-plated zinc, 400 lbs pull out strength, 300 lbs slip strength, 3/8"-16 thread size
Product Type	4D Dovetail Twirl-Nut, 1/4"-20 Thread, 1/4" Nut, ZN PLTD

### Manufacturer Information

Brand	Eaton
GTIN	00799038583127
Manufacturers Part Number	4DTN224ZN
UPC	799038583127

### Taxonomies, Classifications, and Categories

Category Description	SPRING NUTS & TWIRL NUTS
Type	Strut channel nuts



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 East 4th Street  
79720-0000, TX Big Spring  
Phone: 432-264-0316  
Fax: 432-264-0483

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Package ..... 100

Weight Per each ..... 0.044

## Uses, Certifications, and Standards

standard ..... Not Applicable