



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5262WSP TVSS Recept 15A 125V Alarm WH

Pass & Seymour/LeGrand

| | |
|------------------|---|
| Catalog Number | 5262WSP |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Extra Heavy-Duty Surge Protective Duplex Receptacle Offers Increased Transient Protection, Reliability and Protection Notification (Audible Alarm With Led Indicator). Back and, Side Wire, 15AMP 125VOLT, White. |
| Weight per unit | 0.3712 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|--|
| amperage rating | 15 |
| connection | Back and side wire |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | #14 - #10 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | White |
|-------|-------|

Dimensions and Weight

| | |
|--------|------|
| Height | 3.75 |
| Width | 1.25 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | TVSS RECP 15A 125V ALARM WH |
| extra long description | P&S 5262WSP TVSS RECP 15A 125V ALAR |
| Long Description | Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and, Side Wire, 15amp 125volt, White. |
| Product Type | TVSS Recp 15A 125V Alarm WH |
| Special Features | Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place. LED Indication: steady green = protected, flashing red = not protected, OFF = no power to unit. Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation. Impact-resistant nylon exterior resists impacts and scrapes. Triple-wipe, copper-alloy contacts for superior, more dep |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007193893 |
| Manufacturers Part Number | 5262-WSP |
| UPC | 785007193893 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Commercial receptacles |
| Type | Spec Grade Surge Protective Receptacle, Audible Alarm with LED Indicator |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.3712 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-15R |
| standard | ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).;CSA C22.2 No. 42;cUL UL1449, UL498 |
| Temperature Rating | Operating Temperature: -20°C to +55°C (-4°F to 131°F), Storage Temperature: -40°C to +85°C (-40°F to 185°F) |