

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301480083](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Safeway Duplex Heavy - Duty Spec - Grade Receptacle, 2 Pole/3 Wire, NEMA 5-15, 125V, Brown

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                      E46237

**General**

Product Family                      Wiring Devices  
 Series                      [130148](#)  
 IP Rating                      N/A  
 NEMA Configuration                      NEMA 5-15  
 Overview                      [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No                      987650-8068  
 Product Name                      Safeway  
 Receptacle Type                      Duplex  
 Specialty                      N/A  
 Type                      Receptacle  
 UPC                      78678871864  
 Woodhead                      Yes

**Physical**


Flange                      No  
 Flip Lid                      No  
 Gender                      Female  
 Length                      N/A  
 Locking Blade                      No  
 Net Weight                      84.821/g  
 Poles                      2-pole/3-wire

**Electrical**

Cord Type                      N/A  
 Current - Maximum per Contact                      15.0A  
 GFCI                      No  
 Lighted Connector                      No  
 Voltage - Maximum                      125V

**Material Info**

Engineering Number                      5262DW



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130148 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301480083](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Safeway Duplex Heavy - Duty Spec - Grade Receptacle, 2 Pole/3 Wire, NEMA 5-15, 125V, Brown

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E46237

**General**

Product Family                      Wiring Devices  
 Series                                  [130148](#)  
 IP Rating                                N/A  
 NEMA Configuration                NEMA 5-15  
 Overview                               [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No        987650-8068  
 Product Name                         Safeway  
 Receptacle Type                      Duplex  
 Specialty                                N/A  
 Type                                       Receptacle  
 UPC                                        78678871864  
 Woodhead                                Yes

**Physical**


Flange                                    No  
 Flip Lid                                  No  
 Gender                                  Female  
 Length                                  N/A  
 Locking Blade                         No  
 Net Weight                              84.821/g  
 Poles                                      2-pole/3-wire

**Electrical**

Cord Type                                N/A  
 Current - Maximum per Contact    15.0A  
 GFCI                                        No  
 Lighted Connector                    No  
 Voltage - Maximum                    125V

**Material Info**

Engineering Number                    5262DW



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**China RoHS**

**Search Parts in this Series**

[130148 Series](#)