ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



53350 HBL 2G WP BX,(4)1/2HUBS GRY

HUBBELL INCORPORATED DELAWARE

Catalog Number	53350
Manufacturer	HUBBELL INCORPORATED DELAWARE
Description	2G WEATHERPROOF BOX (4) 1/2 IN. OUTLETS - GRAY
Weight per unit	0.9960 (lbs/each)
Product Category	Outlet Boxes, Etc. - Steel

Features

Knockouts	FALSE
Material	Aluminum
Packaging Type	Shrinkwrap
Number Of Outlet	4
Pallet Quantity	864

Material, Color, and Finish

Color	Gray

Dimensions and Weight

Depth	2.25
Size	4.5 H x 4.5 W x 2.125 D
Width	4.5

Descriptions

Construction	Metallic
Description	HBL 2G WP BX,(4)1/2HUBS GRY
Long Description	2G WEATHERPROOF BOX (4) 1/2 IN. OUTLETS - GRAY
Product Type	Weatherproof Boxes & Extensions
	2G WP Box (4) 1/2 In. Outlets - Gray
Special Features	Weatherproof NEMA 3R rated, 2 INes deep with lugs, four threaded outlets, two closure plugs included, reinforced outlets, powder coat finish, ground screw installed, multi-lingual instructions included
Extra Long Description	RACO 5335-0 2G WP BOX (4) 1/2 IN. O

Manufacturer Information

Brand	BELL
	Raco-Taymac-Bell, a Hubbell affiliate
GTIN	00050169533505
Manufacturers Part Number	5335-0
UPC	565656

Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	2-Gang

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	12
Standard Package	12
Weight Per Each	0.9960 (lbs/each)

Uses, Certifications, and Standards

Application	Electrical
Standard	UL Listed;CSA Certified

2-Gang Weatherproof Box, Four 1/2 in. Threaded Outlets, Gray

By Bell
Catalog # 5335-0



2-Gang Weatherproof Box, Four 1/2 in. Threaded Outlets, Gray

Features

- Rugged die-cast aluminum construction
- State-of-the-art powder coat finish providess maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Includes two 1/2 in. closure plugs
- Internal hub threads comply with NEMA requirements and will accept all threaded fittings and threaded conduit
- Ground screw installed
- Multi-lingual instructions in each package

General

Catalog Number	5335-0
Color	Gray
Construction	Metallic
EU RoHS Exemption	6b
EU RoHS Indicator	Yes
Material	Aluminum
Number Of Outlets	4
Number of Gang(s)	2-Gang
Thread Size	1/2 in
Type	2-Gang
UPC	050169533505

Dimensions

Actual Depth	2.25 in
Cubic Capacity	31 cu.in
Depth	2 in
Height	4.5 in
Weight	0.996 lb
Width	4.5 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	• UL Listed • CSA Certified
Nema Rating	NEMA 3R

Logistics

Carton Quantity	12
Packaging Type	Shrink Wrapped
Standard Package	12

Product Assets

Catalogs - RACO / TayMac / Bell Full Catalog
Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50
Certifications - UL COC - E195978-2
Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice
Sales Drawings - 53350 Customer Drawing
SDS - HCC SDS
Terms and Conditions - HCC Terms & Conditions

©2024 Hubbell Incorporated. All rights reserved