



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5362WSP TVSS Recept 20A 125V Alarm WH

Pass & Seymour/LeGrand

Catalog Number	5362WSP
Manufacturer	Pass & Seymour/LeGrand
Description	Surge Protective Extra Heavy-Duty Duplex Receptacle Offers Increased Transient Protection, Reliability and Protection Notification (Audible Alarm With Led Indicator). Specification Grade Surge Suppressor Receptacle With Audible Alarm and Led Indicator, Ideal For Heavy Duty Power Applications. By Pass and Seymour. Back and Side Wire, 20A, 125V.
Weight per unit	0.3712 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Material	Nylon
media	Yes
Number of Wires	3
Poles	2
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10

Material, Color, and Finish

Color	White
Finish	Matte

Dimensions and Weight

Height	3.75
Width	1.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TVSS RECP 20A 125V ALARM WH
extra long description	P&S 5362WSP TVSS RECP 20A 125V ALAR
Long Description	Surge Protective Extra Heavy-Duty Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Specification grade surge suppressor receptacle with audible alarm and LED indicator, ideal for heavy duty power applications. By Pass and Seymour. Back and Side Wire, 20A, 125V.
Product Type	TVSS Recp 20A 125V Alarm WH
Special Features	Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place. LED Indication: steady green = protected, flashing red = not protected, OFF = no power to unit. Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation. Impact-resistant nylon exterior resists impacts and scrapes. Triple-wipe, copper-alloy contacts for superior, more dep

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007193442
Manufacturers Part Number	5362-WSP
UPC	785007193442

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Spec Grade Surge Protective Receptacle, Audible Alarm with LED Indicator

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	50
Weight Per each	0.3712



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	cULus
Temperature Rating	Operating Temperature: -20°C to +55°C (-4°F to 131°F), Storage Temperature: -40°C to +85°C (-40°F to 185°F)