




## SINGLE GANG EXTENSIONS & ADAPTERS

1-1/2 in. Deep Swing Arm Extension Adapters with Lugs - Six Threaded Outlets - 5-1/4 in. x 3-1/2 in.  
N/A

D05



Catalog #: 5415-0

### APPLICATIONS

Used to provide additional capacity needed for NEC box fill requirements  
Adapters allow installer to add "take-offs" to new boxes/devices

### PRODUCT FEATURES

- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Closure plugs provided for two and six outlet styles
- Internal threads and hubs comply with NEMA requirements
- Hubs accept all threaded fittings and threaded conduit
- Multi-lingual instructions in each package
- Includes gasket and mounting hardware
- N/A

### UL LISTED

File E195978

### CSA

C22.2 No. 18

### NEMA

3R Rated

### GENERAL PRODUCT INFORMATION

Color: Gray

### CONFIGURATION

Number Of Outlets: 6  
Gangs: 1

### PRODUCT MEASUREMENTS

Depth: 1-1/2 in.  
Outlet Size: 3/4 in.  
Cubic Inches (cm3): 12.8 (209.8)  
Wt. Ea. (Lbs.): 0.245

### PACKAGING


Package Type: Shrink  
Std. Pkg.: 10  
Product UPC-A Labeled: Yes  
Ship Carton Length (in.): 13.19  
Ship Carton Width (in.): 4.25  
Ship Carton Height (in.): 8.50  
Ctn Weight (Lbs.): 2.45  
Pallet Qty: 1800.00  
UPC Number: 050169541500  
I2of5: 50050169541505



## SINGLE GANG EXTENSIONS & ADAPTERS

1-1/2 in. Deep Swing Arm Extension Adapters with Lugs - Six Threaded Outlets - 5-1/4 in. x 3-1/2 in.  
N/A

D05



Catalog #: 5415-0

### APPLICATIONS

Used to provide additional capacity needed for NEC box fill requirements  
Adapters allow installer to add "take-offs" to new boxes/devices

### PRODUCT FEATURES

- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Closure plugs provided for two and six outlet styles
- Internal threads and hubs comply with NEMA requirements
- Hubs accept all threaded fittings and threaded conduit
- Multi-lingual instructions in each package
- Includes gasket and mounting hardware
- N/A

### UL LISTED

File E195978

### CSA

C22.2 No. 18

### NEMA

3R Rated

### GENERAL PRODUCT INFORMATION

Color: Gray

### CONFIGURATION

Number Of Outlets: 6  
Gangs: 1

### PRODUCT MEASUREMENTS

Depth: 1-1/2 in.  
Outlet Size: 3/4 in.  
Cubic Inches (cm3): 12.8 (209.8)  
Wt. Ea. (Lbs.): 0.245

### PACKAGING

Package Type: Shrink  
Std. Pkg.: 10  
Product UPC-A Labeled: Yes  
Ship Carton Length (in.): 13.19  
Ship Carton Width (in.): 4.25  
Ship Carton Height (in.): 8.50  
Ctn Weight (Lbs.): 2.45  
Pallet Qty: 1800.00  
UPC Number: 050169541500  
I2of5: 50050169541505