


# MULTI-GROOVE FIBERGLASS FISH TAPES



**MULTI-GROOVE  
TECHNOLOGY**



**Low Friction,  
Easy Feed Design**

**Fiberglass Performance  
at 25% Lower Cost!\***

**KLEIN  
TOOLS** 

For Professionals... Since 1857<sup>®</sup> USA

# Multi-Groove Fiberglass Fish Tapes


## Fiberglass Performance

*at 25% Lower Cost!\**




### MULTI-GROOVE TECHNOLOGY

Low friction,  
*easy feed design*



OLD PROFILE



NEW PROFILE



*Less surface contact with wires*

### Fiberglass core and grooves provide:

- Rigidity for long distance.
- Less surface contact when pushing through crowded conduit.

### TWO TIP OPTIONS

#### Multi-Groove Fiberglass Fish Tapes – 7" Spiral Steel Leader

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56055	56055-2	100'L x 3/16"W (7"leader)	13" (330 mm)	3.09 lbs.
56056	56056-9	200'L x 3/16"W (7"leader)	17" (432 mm)	6.16 lbs.



#### Multi-Groove Fiberglass Fish Tapes – Non-Conductive

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56057	56057-6	50'L x 3/16"W	13" (330 mm)	2.33 lbs.
56058	56058-3	100'L x 3/16"W	13" (330 mm)	3.05 lbs.
56059	56059-0	200'L x 3/16"W	17" (432 mm)	6.04 lbs.




**⚠WARNING:** Never remove screws while fish tape is coiled inside reel.



\* When compared to published price of Klein Tools round fiberglass fish tapes.

# MULTI-GROOVE FIBERGLASS FISH TAPES



**MULTI-GROOVE  
TECHNOLOGY**



**Low Friction,  
Easy Feed Design**

**Fiberglass Performance  
at 25% Lower Cost!\***

**KLEIN  
TOOLS** 

For Professionals... Since 1857<sup>®</sup> USA

# Multi-Groove Fiberglass Fish Tapes


## Fiberglass Performance

*at 25% Lower Cost!\**



### MULTI-GROOVE TECHNOLOGY

Low friction,  
*easy feed design*



OLD PROFILE



NEW PROFILE



*Less surface contact with wires*


### Fiberglass core and grooves provide:

- Rigidity for long distance.
- Less surface contact when pushing through crowded conduit.

### TWO TIP OPTIONS

#### Multi-Groove Fiberglass Fish Tapes – 7" Spiral Steel Leader

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56055	56055-2	100'L x 3/16"W (7"leader)	13" (330 mm)	3.09 lbs.
56056	56056-9	200'L x 3/16"W (7"leader)	17" (432 mm)	6.16 lbs.



#### Multi-Groove Fiberglass Fish Tapes – Non-Conductive

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56057	56057-6	50'L x 3/16"W	13" (330 mm)	2.33 lbs.
56058	56058-3	100'L x 3/16"W	13" (330 mm)	3.05 lbs.
56059	56059-0	200'L x 3/16"W	17" (432 mm)	6.04 lbs.



**⚠WARNING:** Never remove screws while fish tape is coiled inside reel.



\* When compared to published price of Klein Tools round fiberglass fish tapes.