



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5P550R 7121 Eaton Us 550VA 120/120VAC Rack *Eaton Power Quality*

Catalog Number	5P550R
Manufacturer	Eaton Power Quality
Description	Eaton 5P Ups, 1U, 550 Va, 420 W, 5-15P Input, Outputs: (5) 5-15R, 120V
Weight per unit	23.8 (lbs/each)
Product Category	Uninterruptible Power Supplies

### Features

accessories	Quick Start Guide
battery	Sealed, lead-acid
Battery Type	VRLA
dimensions	14.3000 IN X 17.4000 IN X 1.7000 IN
Phase	1 PH
Voltage Rating	151/153 V
Wattage	420 W

### Dimensions and Weight

Height	3.4 in
Length	HK 403
Width	3010-2

### Descriptions

Description	7121 EATON US 550VA 120/120VAC RACK
extra long description	ETN 5P550R EATON 5P RACKMOUNT 1U UP
Features	The Eaton 5P UPS delivers reliable backup power in tower and various rackmount form factors for enterprise and distributed IT applications. As the first in the UPS industry to comply with the UL 2900-2-2 cybersecurity standard, Eaton's optional gigabit network card (NETWORK-M2) provides remote monitoring and management for the 5P family of products. When paired with Eaton Intelligent Power Manager (IPM) software, IT professionals can seamlessly manage their connected equipment install base, even in virtual
Long Description	Eaton 5P UPS, 1U, 550 VA, 420 W, 5-15P input, Outputs: (5) 5-15R, 120V
Product Type	Eaton 5P Rackmount 1U Ups
Special Features	ROO/RPO: Rear terminal block connector for remote on/off and power off



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Eaton
GTIN	00743172043030
Manufacturers Part Number	5P550R
UPC	743172043030

## Taxonomies, Classifications, and Categories

Category Description	SURGE SUPPRESSION PRODUCTS
Type	UPS

## Packaging

Carton	1
Weight Per each	23.8

## Uses, Certifications, and Standards

Application	Backup Power and Electronic Power Conversion
Frequency Rating	40/50/60
standard	UL 497A ,cULus Listed ,cUL Listed ,IEC 62040-2 C1-C2 / EN 55024 / CISPR22 Class B / FCC part 15 Class B ,UL 1778,FCC Part 15 Class A Subpart B Sections 15.107b , 15.109b ,RoHS Compliant ,CE Marked