



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



60361212 Encl 60X36X12 N12 1DR CH Clamp CVR *Cooper B-Line/Cable Tray*

Catalog Number	60361212
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 60" Height, 12" Length, 36" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Large Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	147.3 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	12.0000 IN X 36.0000 IN X 60.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	36.00 In Width X 12.00 In Depth X 60.00 In Height
------	---

Descriptions

Description	ENCL 60X36X12 N12 1DR CH CLAMP CVR
extra long description	B-LINE 603612-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 60" height, 12" length, 36" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Large single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 60X36X12
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051804706
Manufacturers Part Number	603612-12
UPC	782051804706

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	147.3

Uses, Certifications, and Standards

Application	Other IT and Datacom - IT and Datacomm - OtherCommercial / Institutional Buildings / Structures - Commercial/Inst Bldg Strctures - AftermarketCommercial / Institutional Buildings / Structures - Building Automation and MonitoringCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Safety and Security SystemsUtility - Substations, Utility Transmission and DistributionDatacenters - IT Space: CI and Hype
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	CSA C22.2.,NEMA,UL 508A