











Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/ Lamp Compatibility
 <p>Baffle</p>	 <p>8 3/16" x 9 1/8"</p>	5-1/2" x 6-7/8"	604 BBRZ 604 BBL 604 BSC 604 BWH 604 WWH	6" Super Slope Downlight Baffle Trim - Black Baffle, Bronze Trim Ring 6" Super Slope Downlight Baffle Trim - Black Baffle, Black Trim Ring 6" Super Slope Downlight Baffle Trim - Black Baffle, Satin Chrome Trim Ring 6" Super Slope Downlight Baffle Trim - Black Baffle, White Trim Ring 6" Super Slope Downlight Baffle Trim - White Baffle, White Trim Ring IC928: 90W PAR38 TC928/TC928R: 150W PAR38 ICPL928 42W ICPL928R 32W IC928LED: G4 09LM, WD G4 09LM/G4 14LM
 <p>Cone</p>	 <p>8 3/16" x 9 1/8"</p>	5-3/4" x 7"	602 CWH 602 HZSC 602 HZWH 602 WHZABZ 602 WHZWH 602 WWH	6" Super Slope Downlight Cone Trim - Clear Alzak® Cone, White Trim Ring 6" Super Slope Downlight Cone Trim - Haze Cone, Satin Chrome Trim 6" Super Slope Downlight Cone Trim - Haze Cone, White Trim Ring 6" Super Slope Downlight Cone Trim - Wheat Haze Cone, Classic Aged Bronze Trim Ring 6" Super Slope Downlight Cone Trim - Wheat Haze, White Trim 6" Super Slope Downlight Cone Trim - White Cone, White Trim Ring IC928: 75W PAR30, 90W PAR38, 85W BR30 TC928/TC928R: 75W PAR30, 150W PAR38, 85W BR30 ICPL928 42W ICPL928R 32W IC928LED: G4 09LM, WD G4 09LM/G4 14LM
 <p>Cylinder Spotlight in Baffle</p>	 <p>9 1/8"</p>		606 BWH 606 WWH	6" Adjustable Cylinder Spotlight in Baffle Trim - Black Baffle, White Trim Ring 6" Adjustable Cylinder Spotlight in Baffle Trim - White Baffle, White Trim Ring IC928/TC928/TC928R: 60W PAR16
 <p>Lensed Flat Diffuser</p>	 <p>9 1/8"</p>		603 BWH 603 WWH	6" Lensed Flat Diffuser Trim - Black Baffle, White Trim Ring 6" Lensed Flat Diffuser Trim - White Baffle, White Trim Ring IC928: 50W PAR30 TC928/TC928R: 75W A19, 75W PAR30
 <p>Baffle, Regressed Frosted Dome Lens</p>	 <p>9 1/8"</p>		6033 WWH	6" Lensed Baffle with Regressed Frosted Dome Lens Trim - White Baffle, White Trim Ring ICPL928 42W (32W rating max) ICPL928R 32W (26W rating max) IC928LED: G4 09LM, WD G4 09LM/G4 14LM

Housing and trim can be ordered together or separate, but will always ship separately.