



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



61065 Vol-Test Voltage Tester

Ideal

| | |
|------------------|--|
| Catalog Number | 61065 |
| Manufacturer | Ideal |
| Description | Ideal, Voltage Tester, Vol-Test, Solenoid, Voltage Rating: 600 V, Warranty: 2 Year |
| Weight per unit | 0.8000 (lbs/each) |
| Product Category | Testers & Accessories |

Features

| | |
|----------------|-----|
| Voltage Rating | 600 |
|----------------|-----|

Descriptions

| | |
|------------------------|--|
| Description | VOL-TEST VOLTAGE TESTER |
| extra long description | IDEAL 61-065 Voltage Tester,Ideal,V |
| Features | Extremely rugged and reliableVibrates when AC voltage is presentIndicates AC/DC voltage levelReplaceable leads with shielded probe tips (IEC61010-031 compliant)Bright, long-life LED's and neon indicator lampLow impedance to eliminate ghost voltagesDual voltage indication for backup safety2-year warranty |
| Long Description | IDEAL, Voltage Tester, Vol-Test, Solenoid, Voltage Rating: 600 V, Warranty: 2 year |
| Product Type | Voltage Tester, Ideal, Vol-Test, Sol, C/Us UI Listed, Cat Iii, 600 |
| Special Features | Features: Extremely Rugged And Reliable; Solenoid Indicator And Neon Test Lamp Provide Double Protection; Tests 80V To 600V AC/DC (25 to 60Hz); Independent Circuitry Provides A Built-In Backup Safety System; Replaceable Leads With Shielded Probe Tips; 2-Year Warranty; CAT III - 600V; Warranty: 2 year |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250610655 |
| Manufacturers Part Number | 61-065 |
| UPC | 783250610655 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
| Type | Solenoid |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.8 |

Uses, Certifications, and Standards

| | |
|----------|-------------------------|
| standard | C/US UL Listed, CAT III |
|----------|-------------------------|