

**NEW!**  
See  
reverse

# Versatile IN AND OUT™ Cover

*Low profile when not in use – Weatherproof while in use*



**IN** for  
**GOOD LOOKS!**

**Paintable  
White Cover**  
VERTICAL  
Standard size: **60VW**



**OUT**  
to **PLUG IN**




*Lift sides and press  
down to go back IN.*

Arlington's **IN AND OUT™ Cover** is a low profile cover when *not in use* and a deeper, weatherproof in use cover when a cord's plugged in!

In the *IN* position the cord holes at the bottom of the box are sealed to keep bugs out. But it extends quickly and easily into the *OUT* position to accommodate a plug, then back again to a low profile cover.

- Fits over all boxes or openings in new or existing projects
- Two sizes: Standard to fit over a regular size outlet or FS box and oversized, with a one-piece base plate/gasket combination that fits larger openings or a 3.5" round outlet box
- Removable cover for easier installation
- Colors: Paintable white or clear
- Vertical and horizontal styles
- Competitively priced
- UL Listed weatherproof while in use installation



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)

Patent pending

# Vertical & Horizontal IN AND OUT™ Cover

*Two sizes: Standard and Oversized combination plate/gasket*



## Fast, easy installation

Installation of the IN AND OUT cover with oversize base for large openings or 3.5" round boxes is shown here.


- 1 Pull device out of box as necessary.
- 2 Feed device through opening in base (cover is removable for easier access), and...
- 3 Install device through the pre-drilled holes in base.
- 4 Install plate and the installation is done!



## Paintable White Cover

for standard boxes:

**60VW**




**60HW**

for oversized openings or 3.5" round boxes:

**61VW**



**61HW**



## IN AND OUT Cover

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description	Std Pkg	Cover Color
<b>60VW</b>	00680	Standard base/Vertical	4	White
<b>61VW</b>	00681	Oversize base/Vertical	4	White
<b>60VC</b>	00682	Standard base/Vertical	4	Clear
<b>61VC</b>	00683	Oversize base/Vertical	4	Clear
<b>60HW</b>	00684	Standard base/Horizontal	4	White
<b>61HW</b>	00685	Oversize base/Horizontal	4	White
<b>60HC</b>	00686	Standard base/Horizontal	4	Clear
<b>61HC</b>	00687	Oversize base/Horizontal	4	Clear

Standard base fits regular-size outlet boxes.

Oversized base plate/gasket fits larger openings or a 3.5" round outlet box.




**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
www.aifittings.com

## Clear Cover


for standard boxes:

**60VC**



for oversized openings:

**61HC**



Distributed by

**NEW!**  
See  
reverse

# Versatile IN AND OUT™ Cover

*Low profile when not in use – Weatherproof while in use*



**IN** for  
**GOOD LOOKS!**

**Paintable  
White Cover**  
VERTICAL  
Standard size: **60VW**



**OUT**  
to **PLUG IN**




*Lift sides and press  
down to go back IN.*

Arlington's **IN AND OUT™ Cover** is a low profile cover when *not in use* and a deeper, weatherproof in use cover when a cord's plugged in!

In the *IN* position the cord holes at the bottom of the box are sealed to keep bugs out. But it extends quickly and easily into the *OUT* position to accommodate a plug, then back again to a low profile cover.

- Fits over all boxes or openings in new or existing projects
- Two sizes: Standard to fit over a regular size outlet or FS box and oversized, with a one-piece base plate/gasket combination that fits larger openings or a 3.5" round outlet box
- Removable cover for easier installation
- Colors: Paintable white or clear
- Vertical and horizontal styles
- Competitively priced
- UL Listed weatherproof while in use installation



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com) Patent pending

# Vertical & Horizontal IN AND OUT™ Cover

*Two sizes: Standard and Oversized combination plate/gasket*



## Fast, easy installation

Installation of the IN AND OUT cover with oversize base for large openings or 3.5" round boxes is shown here.


- 1 Pull device out of box as necessary.
- 2 Feed device through opening in base (cover is removable for easier access), and...
- 3 Install device through the pre-drilled holes in base.
- 4 Install plate and the installation is done!



## Paintable White Cover

for standard boxes:

**60VW**




**60HW**

for oversized openings or 3.5" round boxes:

**61VW**

**61HW**



## IN AND OUT Cover

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description	Std Pkg	Cover Color
<b>60VW</b>	00680	Standard base/Vertical	4	White
<b>61VW</b>	00681	Oversize base/Vertical	4	White
<b>60VC</b>	00682	Standard base/Vertical	4	Clear
<b>61VC</b>	00683	Oversize base/Vertical	4	Clear
<b>60HW</b>	00684	Standard base/Horizontal	4	White
<b>61HW</b>	00685	Oversize base/Horizontal	4	White
<b>60HC</b>	00686	Standard base/Horizontal	4	Clear
<b>61HC</b>	00687	Oversize base/Horizontal	4	Clear

Standard base fits regular-size outlet boxes.

Oversized base plate/gasket fits larger openings or a 3.5" round outlet box.




**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
www.aifittings.com

## Clear Cover


for standard boxes:

**60VC**



for oversized openings:

**61HC**



Distributed by