



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65573807 14/4 Seoww Yellow 250' *Southwire Company*

| | |
|------------------|---|
| Catalog Number | 65573807 |
| Manufacturer | Southwire Company |
| Description | 14-41 Cu 4/C Black/White/Red/Green Seoww (Tpe/Stoow) Yellow 105C 600V Poly 250SP |
| Weight per unit | 0.1210 (lbs/ft) |
| Product Category | Wire |

Features

| | |
|----------------------|-------|
| Conductor Size | 14 |
| connector | N/A |
| core | 14 |
| insulation | PVC |
| media | Yes |
| Number of Conductors | 4 |
| Number of Outlets | N/A |
| outside diameter | 0.568 |
| Plug Type | N/A |
| strands | 65 |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|--------------------|--------|
| Color | Yellow |
| Conductor Material | Copper |

Dimensions and Weight

| | |
|--------|-----|
| Length | 250 |
|--------|-----|

Descriptions

| | |
|------------------------|---|
| Construction | TPE JACKET |
| Description | 14/4 SEOWW YELLOW 250' |
| extra long description | SWC 65573807 FLEXCORD 14/4 SEOWW 10 |
| Long Description | 14-41 CU 4/C BLACK/WHITE/RED/GREEN SEOWW (TPE/STOOW) YELLOW 105C 600V POLY 250Sp |
| Product Type | Flexcord 14/4 Seoww 105C Yw 250SP |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cables & Cords |
| GTIN | 00032886939761 |
| Manufacturers Part Number | 65573807 |
| UPC | 032886939761 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Portable Cords, Voice, Data, Video Wire & Cable |
| Type | SEOOW |

Packaging

| | |
|-----------------|-------|
| Carton | 250 |
| Weight | 45.72 |
| Weight Per foot | 0.121 |

Uses, Certifications, and Standards

| | |
|-------------|----------|
| Application | FLEXCORD |
| standard | UL62 |