ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3101 Industrial Terrace
78758-0000, TX Austin
Phone: 512-351-3290
Fax: 512-973-9027



65931 20W Led Bullet Security Flood W/Smart Camera - BLK

Satco

Catalog Number	65931
Manufacturer	Satco
Description	20 Watt Bullet Outdoor Smart Security Light With Camera - Starfish Enabled - 3K/4K/5K CCT Selectable - Black Finish
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.167 to 0.722
Lamp Type	LED
Number of Lamps	2
Power Factor	N/A
Power Rating	20
Reflector Type	Semi-Frost
Socket Type	Integrated
Voltage Rating	120 to 277

Material, Color, and Finish

fixture material	Die-Cast Aluminum / Plastic
Style	Utility

Dimensions and Weight

Size	W:8.60 H:6.31 E:7.32

Descriptions

Description	20W LED BULLET SECURITY FLOOD W/SMART CAMERA - BLK
extra long description	SATCO 65/931 BULLET SEC LGT W/ CAM-
Long Description	20 Watt Bullet Outdoor SMART Security Light with Camera - Starfish Enabled - 3K/4K/5K CCT Selectable - Black Finish
Product Type	Bullet Sec LGT W/ Cam-Bla
Special Features	Warranty: 1-Year ; Installation Notes: Designed for Recessed or External Junction Boxes ; FCC Compliant: True ; Cct Selectable: True ; CCT (Kelvin Temp): 3000K/4000K/5000K ; Hours Rated: 50000 ; Beam Angle (degree): 70 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Semi-Frost ; Lens Material: Polycarbonate (PC) ; Operating Temp: -20C (-4F) to +45C (+113F) ; Watts: 20W ; Lumens: 1600L/1750L ; Sensor Field Of View: 90 to 100 degrees

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3101 Industrial Terrace
78758-0000, TX Austin
Phone: 512-351-3290
Fax: 512-973-9027

Manufacturer Information

Brand	Nuvo
GTIN	00045923657603
Manufacturers Part Number	65/931
UPC	045923657603

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Commercial LED

Packaging

Carton	1
Weight Per each	1.43

Uses, Certifications, and Standards

Application	Outdoor
environmental conditions	Wet
Frequency Rating	50/60
standard	cETLus - Listed