



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65BEMWHLSWW590CR 6" 12W Led Trim 1200LM Color Selectable

Lithonia Lighting

Catalog Number	65BEMWHLSWW590CR
Manufacturer	Lithonia Lighting
Description	Experience The Ultimate 5-In-1 Solution With E Series Switchable White Led Trim Kits. Offering Flexibility At Your Fingertips, E Series Trim Kits Feature A Switch, Located Directly On The Fixture, That Allows You to Choose Between 5 Color Temperature Options Ranging From 2700K (Warm White) to 5000K (Daylight). Available In 5/6" Size, The E Series Provides Easy Retrofitting From Below The Ceiling or Can Be Paired With A Juno® Quick Connect QC Series Recessed Housing For New Construction Applications.
Weight per unit	0.7000 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	7.625 x 7.625 x 3.667
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1200 LM,900 LM
Material	Aluminum
media	Yes
Number of Lamps	1
Reflector Type	Aluminum Spun
Shape	Round
Socket Type	N/A
Voltage Rating	120 V
Warranty	5
Wattage	13.9

Material, Color, and Finish

Color	White
Finish	Matte
Style	CONTEMPORARY

Dimensions and Weight

Height	4.125
Length	7.625
Width	7.625



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Retrofit
Description	6" 12W LED TRIM 1200LM COLOR SELECTABLE
extra long description	LITH 65BEMW HL SWW5 90CRI M6 6IN Ju
Features	Design Select
Long Description	Experience the ultimate 5-in-1 solution with E Series Switchable White LED Trim Kits. Offering flexibility at your fingertips, E Series Trim Kits feature a switch, located directly on the fixture, that allows you to choose between 5 color temperature options ranging from 2700K (Warm White) to 5000K (Daylight). Available in 5/6" size, the E Series provides easy retrofitting from below the ceiling or can be paired with a Juno® Quick Connect QC Series recessed housing for new construction applications.
Product Type	Trim
Special Features	Switchable Color Temperature

Manufacturer Information

Brand	JUNO
GTIN	00194994244950
Manufacturers Part Number	65BEMW HL SWW5 90CRI M6
UPC	194994244950

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Trim

Trade Size

aperture size	5 IN,6 IN
---------------	-----------

Packaging

Carton	1
Package	6
Weight Per each	0.7

Uses, Certifications, and Standards

Application	Hospitality,Residential,Retail,Retrofit
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 20,CA Title 24,ENERGY STAR,JA8