



## METACALK® FIRESTOP SEALANTS

### Metacaulk® 1000

Intumescent, water-based firestop sealant

Code	Description	Qty.
66640	10.3 oz. cartridge	12
66303	30 oz. cartridge	12
66312	20.2 oz. sausage pack	12
66305	1 gal.	4
66307	2 gal.	1
66309	5 gal.	1

**Application** • Will prevent the spread of fire through joint openings and through-penetrations  
 • No dilution or mixing required • Can be used in areas under constant vibration and movement  
 • Use in fire-rated gypsum wallboard partitions, concrete walls or floors, wood floors and concrete or corrugated steel deck floor/ceiling assemblies

**Recommended for** • Metal • Insulated  
 • Fiberglass & plastic pipes • Wall construction joints • Power & telephone cables



#### FEATURES

- UL Classified systems up to 4 hrs.
- Highly intumescent
- Excellent freeze-thaw
- For interior use - paintable
- VOC compliant
- STC rating 62
- Meets ASTM E 814, UL 1479 & UL 2079 standards

See ordering chart for container sizes available.



### Metacaulk® MC 150+

General purpose firestop sealant

Code	Description	Qty.
66648	10.3 oz. cartridge	12
66383	30 oz. cartridge	12
66385	20.2 oz. sausage pack	12
66389	5 gal.	1

**Application** • One component, general purpose fire-rated sealant and smoke seal for construction joints and through-penetrations on both horizontal and vertical surfaces  
 • Non-sag caulking grade sealant that is easy to apply as well as to retrofit • Can be used in areas under constant vibration or movement

**Recommended for**  
 • Metal • Insulated  
 • Fiberglass and plastic pipes  
 • Wall construction joints  
 • Power and telephone cables



#### FEATURES

- Water-based - VOC compliant
- Excellent freeze-thaw
- For interior use - paintable
- Use for most common applications
- STC rating 51



\*FBC™ System Compatible™ indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® pipe and fittings.  
 \*\*FBC®, FlowGuard Gold®, BlazeMaster® and Corzan® are licensed trademarks of The Lubrizol Corporation.

For Firestopping accessories, visit [www.rectorseal.com/qr/mfa.html](http://www.rectorseal.com/qr/mfa.html) or scan this code.



## METACALK® FIRESTOP SEALANTS

### Metacaulk® 1000

Intumescent, water-based firestop sealant

Code	Description	Qty.
66640	10.3 oz. cartridge	12
66303	30 oz. cartridge	12
66312	20.2 oz. sausage pack	12
66305	1 gal.	4
66307	2 gal.	1
66309	5 gal.	1

**Application** • Will prevent the spread of fire through joint openings and through-penetrations  
 • No dilution or mixing required • Can be used in areas under constant vibration and movement  
 • Use in fire-rated gypsum wallboard partitions, concrete walls or floors, wood floors and concrete or corrugated steel deck floor/ceiling assemblies

**Recommended for** • Metal • Insulated  
 • Fiberglass & plastic pipes • Wall construction joints • Power & telephone cables



#### FEATURES

- UL Classified systems up to 4 hrs.
- Highly intumescent
- Excellent freeze-thaw
- For interior use - paintable
- VOC compliant
- STC rating 62
- Meets ASTM E 814, UL 1479 & UL 2079 standards

See ordering chart for container sizes available.



### Metacaulk® MC 150+

General purpose firestop sealant

Code	Description	Qty.
66648	10.3 oz. cartridge	12
66383	30 oz. cartridge	12
66385	20.2 oz. sausage pack	12
66389	5 gal.	1

**Application** • One component, general purpose fire-rated sealant and smoke seal for construction joints and through-penetrations on both horizontal and vertical surfaces  
 • Non-sag caulking grade sealant that is easy to apply as well as to retrofit • Can be used in areas under constant vibration or movement

**Recommended for**  
 • Metal • Insulated  
 • Fiberglass and plastic pipes  
 • Wall construction joints  
 • Power and telephone cables



#### FEATURES

- Water-based - VOC compliant
- Excellent freeze-thaw
- For interior use - paintable
- Use for most common applications
- STC rating 51



\*FBC™ System Compatible™ indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® pipe and fittings.  
 \*\*FBC®, FlowGuard Gold®, BlazeMaster® and Corzan® are licensed trademarks of The Lubrizol Corporation.

For Firestopping accessories, visit [www.rectorseal.com/qr/mfa.html](http://www.rectorseal.com/qr/mfa.html) or scan this code.