



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



664BKG SW 4W Ac 15A 120V GRD Terminal BK

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 664BKG |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Four-Way Switch, Grounded Terminals, 15 Amps, 120 Volts, Brown. |
| Weight per unit | 0.2072 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|---------------|
| amperage rating | 15 |
| Material | Thermoplastic |
| media | Yes |
| Number of Wires | 4 |
| Poles | 4-Way |
| Voltage | 120.0 V |
| Voltage Rating | 120 |
| Wire Size | 12-14Awg |

Dimensions and Weight

| | |
|------|------|
| Size | 4.2" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | SW 4W AC 15A 120V GRD TERMINAL BK |
| extra long description | P&S 664BKG SW 4W AC 15A 120V GRD TE |
| Long Description | Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, Brown. |
| Product Type | SW 4W Ac 15A 120V GRD Terminal BK |
| Special Features | High impact resistant construction, extra long stap, side wire, push wire |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007664065 |
| Manufacturers Part Number | 664BKG |
| UPC | 785007664065 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.2072 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | CSA, CULUS, UL, UL20 |