



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7100S 1" Emt Steel Comp Connector

Appleton/Oz Gedney

| | |
|------------------|---|
| Catalog Number | 7100S |
| Manufacturer | Appleton/Oz Gedney |
| Description | Emt Compression Connector, 1 In Trade Size, Straight Connection Orientation, Zinc Plated, Non-Insulated, 1.25 In Length, 1.56 In Diameter, 9/16 In Thread Length, 32 LB/100 |
| Weight per unit | 0.2600 (lbs/each) |
| Product Category | Steel Uninsulated Straight Com |

Features

| | |
|----------------|-----------------|
| connection | Male NPS Thread |
| Connector Type | Compression |
| insulation | Non-Insulated |
| Material | Steel |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Metallic |
| Finish | Zinc Electro Plated |

Dimensions and Weight

| | |
|------|---|
| Size | 1 |
|------|---|

Descriptions

| | |
|------------------------|------------------------------|
| Description | 1" EMT STEEL COMP CONNECTOR |
| extra long description | EGS 7100S 1 IN EMT COMP CONN |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Appleton |
| GTIN | 00687855873197 |
| UPC | 687855873197 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL EMT FITTINGS |
| Type | EMT Conduit Straight Compression Connector |

Trade Size

| | |
|------------|---|
| Trade Size | 1 |
|------------|---|

Packaging

| | |
|-----------------|------|
| Carton | 20 |
| Package | 100 |
| Weight Per each | 0.26 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | To ground and secure EMT Raceways to boxes and enclosures |
| nema rating | FB-1 |
| standard | UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507; NEMA: FB-1 |