



Core & Coil (71A) HPS 200W - 400W

CORE & COIL HID HPS BAL 250W S50 5-TAP KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S50
Lamp Type	250W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A8251
Core Size	4 x 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI501-H4
Ignitor Temperature Rating	105°C
Capacitor Value	35 MFD
Capacitor Catalog Number	7C350P24RA
Capacitor Requirements	240V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval	1.65 in
Dimensions	
Capacitor Height	3.7 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	120/208/240/277/480 V
Input Frequency	60 Hz
Input Current (Open Circuit)	1.82/1.1/0.92/0.83/0.45 A
Input Current (Starting)	1.32/0.82/0.66/0.56/0.32 A
Input Current (Short Circuit)	0.81-1.22/0.44-0.66/0.39-0.58/0.32-0.49/0.2-0.3 A
Secondary Short Circuit Current	3.69-4.51 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	188 V
Input Current (Nom)	2.66/1.54/1.32/1.16/0.66 A A
Input Power (Nom)	300 W
Rated Lamp Power	250 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration	Yes
Allowed	


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) HPS 200W - 400W

Max Ballast-Lamp Distance	2'
Remote Wiring	
Recommended Fuse Value	7/4/4/3/2 A
Approval and Application	
Open Circuit Voltage Test (Volts)	169-207 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/B/B/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)

UL Temperature Code	1029C
Product Data	
Order product name	CORE & COIL HID HPS BAL 250W S50 5-TAP KIT
EAN/UPC - Product	781087114193
Order code	913710414701
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710414701
Net Weight (Piece)	5.612 kg

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 250W S50 5-	3.6 in	2 in	4.8 in	4.4 in	4.3 in	3.9 in
TAP KIT						



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.