



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **7401028 STR Male, DCG, 1.1-1.2\", 1.25\" W/Mesh** *Hubbell Wiring Devices*

Catalog Number	7401028
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.125-1.250\", 1 1/4\" With Mesh
Weight per unit	0.5000 (lbs/each)
Product Category	Cable & Cord Grips

### **Features**

Material	Aluminum Fittings, Stainless Steel Mesh
Number of Conductors	Single
pallet quantity	540

### **Material, Color, and Finish**

Color	Metallic
-------	----------

### **Dimensions and Weight**

Size	1 1/4\" NPT
------	-------------

### **Descriptions**

Description	STR MALE, DCG, 1.1-1.2\", 1.25\" W/MESH
extra long description	HWDK 07401028 STR MALE, DCG, 1.1-1.
Features	Deluxe cord grips help to alleviate pull tension on terminals, control cable arc-of-bend, prevent cord pull-out and provide a Liquidtight seal. They are offered with either aluminum, stainless steel or nylon fittings in a variety of configurations and NPT thread sizes. Additionally, a completely non-metallic product is available. Specific uses are: wiring enclosures, pendant stations, hand tools, construction, processing and material handling equipment, pumps, motors and machine tools.
Long Description	Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.125-1.250\", 1 1/4\" with Mesh
Product Type	STR Male, DCG, 1.1-1.2\", 1.25\" W/Mesh
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585322094
Manufacturers Part Number	07401028
series	Deluxe Cord Grips
UPC	783585322094



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Straight Male Thread

## Packaging

Carton	1
Weight Per each	0.5

## Uses, Certifications, and Standards

Application	Straight Male- Form 5
environmental conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Mounting	Locknut or Tapped Opening
standard	UL Listed
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)