

Eaton's Wiring Devices  
Decorator combination devices

# Decorator Combination Devices

Space-saving architectural combination  
devices add elegance and style

**EATON**

*Powering Business Worldwide*

Eaton's Decorator Combination switches add elegance to residential and light commercial applications. Decorator design features easy, smooth actuation of the rocker.



7728



7729



7730

## Switch Combinations

### Product description

Single pole & 3-Way  
120/277V/AC

### Features

- 120/277V/AC rating is ideal for incandescent or fluorescent lighting fixtures
- Thermoplastic rocker, top and backbody are virtually unbreakable to deliver years of durable performance
- Ultrasonic welding and integrated construction of the strap and body provide superior ground integrity even under heavy use
- Durable, injection molded housings and PVC resin comply with UL94 V0 flammability ratings
- Automatic grounding system eliminates the need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where a jumper is used
- Steel mounting strap is zinc-plated for added corrosion resistance
- Backwire clamps on side terminals provide for easy installation of #12 and #14 wire
- Terminal screws are backed out and ready for wiring to enhance ease of installation
- Break-off provision on switches for wiring both devices on the same circuit or on separate circuits
- Triple wipe blade contacts and double wipe ground contacts to insure long-term plug retention (TR7730)


### Decorator combination switches



Catalog no.	Description	Rating		Color suffix
		Watt	V/AC	
□ 7728__	Two single-pole switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7729__	Three single-pole switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7730__	One single-pole switch w/ NEMA 5-15 receptacle	15 15	120 switch 125 receptacle	
□ 7731__	Two 3-way switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7732__	One single-pole switch w/ one 3-way switch, back & side wire	15 15	120 switch 125 receptacle	A, BK, LA, V, W
□ TR7730__	One single-pole switch with one tamper resistant NEMA 5-15R receptacle, back & side wire	15 15	120 switch 125 receptacle	A, BK, LA, V, W

### Color ordering information

For ordering devices, include Catalog no. followed by the color suffix:  
A (Almond), BK (Black), LA (Light Almond), V (Ivory), W (White)



Compliances, specifications and availability are subject to change without notice.

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/wiringdevices

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/wiringdevices

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlán Km 178 s/n  
Col. Villa Jardín esq.  
Cerrada 8 de Mayo  
Cuautitlán, Mexico CP 54800  
México  
Eaton.mx  
Eaton.com/wiringdevices



Eaton's Wiring Devices  
Decorator combination devices

# Decorator Combination Devices

Space-saving architectural combination  
devices add elegance and style

**EATON**

*Powering Business Worldwide*

Eaton's Decorator Combination switches add elegance to residential and light commercial applications. Decorator design features easy, smooth actuation of the rocker.



7728



7729



7730

## Switch Combinations

### Product description

Single pole & 3-Way  
120/277V/AC

### Features

- 120/277V/AC rating is ideal for incandescent or fluorescent lighting fixtures
- Thermoplastic rocker, top and backbody are virtually unbreakable to deliver years of durable performance
- Ultrasonic welding and integrated construction of the strap and body provide superior ground integrity even under heavy use
- Durable, injection molded housings and PVC resin comply with UL94 V0 flammability ratings
- Automatic grounding system eliminates the need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where a jumper is used
- Steel mounting strap is zinc-plated for added corrosion resistance
- Backwire clamps on side terminals provide for easy installation of #12 and #14 wire
- Terminal screws are backed out and ready for wiring to enhance ease of installation
- Break-off provision on switches for wiring both devices on the same circuit or on separate circuits
- Triple wipe blade contacts and double wipe ground contacts to insure long-term plug retention (TR7730)

### Decorator combination switches



Catalog no.	Description	Rating		Color suffix
		Watt	V/AC	
□ 7728__	Two single-pole switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7729__	Three single-pole switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7730__	One single-pole switch w/ NEMA 5-15 receptacle	15 15	120 switch 125 receptacle	
□ 7731__	Two 3-way switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7732__	One single-pole switch w/ one 3-way switch, back & side wire	15 15	120 switch 125 receptacle	A, BK, LA, V, W
□ TR7730__	One single-pole switch with one tamper resistant NEMA 5-15R receptacle, back & side wire	15 15	120 switch 125 receptacle	A, BK, LA, V, W

### Color ordering information

For ordering devices, include Catalog no. followed by the color suffix:  
A (Almond), BK (Black), LA (Light Almond), V (Ivory), W (White)

A	BK	LA	V	W
(Almond)	(Black)	(Light Almond)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/wiringdevices

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/wiringdevices

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlán Km 178 s/n  
Col. Villa Jardín esq.  
Cerrada 8 de Mayo  
Cuautitlán, Mexico CP 54800  
México  
Eaton.mx  
Eaton.com/wiringdevices