

LED step light

| | |
|-----------------|--------------|
| Project Name: | Prepared By: |
| Project Number: | Date: |
| Catalog Number: | Type: |

Description

120V/AC
60Hz

Design features

- Fits into a standard junction box for easy installation (single-gang, handy box, 2" minimum inside width)
- 6 LED's with 6000-6500K light temperature
- Energy-efficient 40,000 hour rated LED lamp light
- Back & side wire, #14 - #12 AWG
- Perfect for any area where low level lighting or safe way-finding is needed, such as hallways, stairways, lobbies, auditoriums and theaters
- Includes vertical and horizontal louvered wallplates



7739W

Table 1. LED Step Light

| Catalog No. | Description | Rating V/AC | Color Suffix |
|-------------|---|----------------|--------------|
| □ 7739__ | 3W LED Step Light (vertical & horizontal) | 120 V/AC, 60Hz | A, LA, W |

Compliances, specifications and availability are subject to change without notice.



Powering Business Worldwide

| | |
|-----------------|--------------|
| Project Name: | Prepared By: |
| Project Number: | Date: |
| Catalog Number: | Type: |

Table 2. Specifications

| Catalog No. | 7739 Series |
|--------------------------------------|---------------------------------------|
| Series Type | LED Step Light |
| Illumination | 6 LEDs LED life rated 40,000 hours |
| Color Temperature | 6000-6500K |
| Power Consumption | < 3 Watts |
| Testing & Code Compliance | cULus Listed UL 1598 and UL8750 |
| Power Supply | 120 V/AC, 60 Hz |
| Installation | Single-gang junction box |

Table 3. Materials


| Catalog No. | 7739 Series |
|-----------------------------------|-------------------|
| Wallplate | Polycarbonate/ABS |
| Bottom Housing | Polycarbonate |
| Strap | Galvanized steel |
| Termination Accommodations | #14-#12 AWG |


Table 4. Color Ordering Information

For ordering devices, include Cat. No. followed by the color code: A (Almond), LA (Light Almond), W (White)

| | | |
|----------|------------|----------|
| A | LA | W |
| Almond | Lt. Almond | White |

Certifications & Compliances

| Catalog No. |  |
|-------------|---|
| 7739 | • |

KEY:  cULus

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 17.8 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Eaton.com/wiringdevices

LED step light

| | |
|-----------------|--------------|
| Project Name: | Prepared By: |
| Project Number: | Date: |
| Catalog Number: | Type: |

Description

120V/AC
60Hz

Design features

- Fits into a standard junction box for easy installation (single-gang, handy box, 2" minimum inside width)
- 6 LED's with 6000-6500K light temperature
- Energy-efficient 40,000 hour rated LED lamp light
- Back & side wire, #14 - #12 AWG
- Perfect for any area where low level lighting or safe way-finding is needed, such as hallways, stairways, lobbies, auditoriums and theaters
- Includes vertical and horizontal louvered wallplates



7739W

Table 1. LED Step Light

| Catalog No. | Description | Rating V/AC | Color Suffix |
|-------------|---|----------------|--------------|
| □ 7739__ | 3W LED Step Light (vertical & horizontal) | 120 V/AC, 60Hz | A, LA, W |

Compliances, specifications and availability are subject to change without notice.



Powering Business Worldwide

| | |
|-----------------|--------------|
| Project Name: | Prepared By: |
| Project Number: | Date: |
| Catalog Number: | Type: |

Table 2. Specifications

| Catalog No. | 7739 Series |
|--------------------------------------|---------------------------------------|
| Series Type | LED Step Light |
| Illumination | 6 LEDs LED life rated 40,000 hours |
| Color Temperature | 6000-6500K |
| Power Consumption | < 3 Watts |
| Testing & Code Compliance | cULus Listed UL 1598 and UL8750 |
| Power Supply | 120 V/AC, 60 Hz |
| Installation | Single-gang junction box |

Table 3. Materials


| Catalog No. | 7739 Series |
|-----------------------------------|-------------------|
| Wallplate | Polycarbonate/ABS |
| Bottom Housing | Polycarbonate |
| Strap | Galvanized steel |
| Termination Accommodations | #14-#12 AWG |

Table 4. Color Ordering Information

For ordering devices, include Cat. No. followed by the color code: A (Almond), LA (Light Almond), W (White)

| | | |
|----------|------------|----------|
| A | LA | W |
| Almond | Lt. Almond | White |

Certifications & Compliances

| Catalog No. |  |
|-------------|---|
| 7739 | • |

KEY:  cULus

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 17.8 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Eaton.com/wiringdevices