

## E26 6" Trim Series


### DESCRIPTION

Eyeball 30° tilt, self-flanged in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

### SPECIFICATION FEATURES

- 30° tilt, 360° rotation
- Torsion spring retention
- Wide choice of finishes for any decor
- Socket supporting eyeball
- 78PAT makes installation Air-Tite regardless of housing used



#### Dimensions:

A: 4" [100mm]  
 H: 4-1/8" [105mm]  
 OD: 8" [203mm]

Housings		Max Lamp Compatibility
H7ICT	H7RICT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
H7ICAT	H7RICAT	
E7ICAT	E7RICAT	75W PAR30S, 75W PAR30L, 65W BR30
H7UICAT		75W PAR30S, 75W PAR30L, 85W BR30, 100W R30
H7ICTNB	H7ICATNB	75W PAR30L, 65W BR30, 75W R30
E7ICATNB		75W PAR30S, 75W PAR30L, 65W BR30
H27ICAT	H27RICAT	75W PAR30L, 65W BR30, 75W R30
E27ICAT	E27RICAT	75W PAR30L, 65W BR30
H7T	H7RT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
H7TCP		75W PAR30S, 75W R30, 65W BR30
E7TAT		75W PAR30S, 75W PAR30L, 65W BR30
E7RTAT		50W PAR30S, 75W PAR30L, 65W BR30
H7TNB		75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
E7TATNB		75W PAR30S, 75W PAR30L, 65W BR30
H645IC		65W BR30, 75W R30, 75W PAR30L
H27T		75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
H27RT		
E27TAT	E27RTAT	75W PAR30S, 75W PAR30L, 65W BR30

Compatible with Halogen, Incandescent, LED\* or CFL\* lamps.



**78P**  
White Trim, White Eyeball



**78PAT**  
White Air-Tite™ Trim, White Eyeball



**78SN**  
Satin Nickel Trim, Satin Nickel Eyeball



**78TBZ**  
Tuscan Bronze Trim, Tuscan Bronze Eyeball

### ORDERING INFORMATION

SAMPLE NUMBER: 78P

Trim	Finish
78P= 6" White Eyeball, White Trim	WH=White Trim
78PAT= 6" White Eyeball, White Trim	WH=White Trim
78SN= 6" Satin Nickel Eyeball, Satin Nickel Trim	SN=Satin Nickel
78TBZ= 6" Tuscan Bronze Eyeball, Tuscan Bronze Trim	TBZ=Tuscan Bronze

### HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
419P	Adjustable	•	•	•	•	•	•	•	•
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		•	•	•	•	•	•		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
•	•	•	•	•	•	•	•	•	
		H27RT	E27TAT	E27RTAT					
		•	•	•					

For use in select other's housings, refer to U.L. classification list at [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



For use in Halo listed housings.



Select trims are classified for use in others housings. See [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).

## E26 6" Trim Series


### DESCRIPTION

Eyeball 30° tilt, self-flanged in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

### SPECIFICATION FEATURES

- 30° tilt, 360° rotation
- Torsion spring retention
- Wide choice of finishes for any decor
- Socket supporting eyeball
- 78PAT makes installation Air-Tite regardless of housing used



#### Dimensions:

A: 4" [100mm]  
 H: 4-1/8" [105mm]  
 OD: 8" [203mm]

Housings		Max Lamp Compatibility
H7ICT	H7RICT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
H7ICAT	H7RICAT	
E7ICAT	E7RICAT	75W PAR30S, 75W PAR30L, 65W BR30
H7UICAT		75W PAR30S, 75W PAR30L, 85W BR30, 100W R30
H7ICTNB	H7ICATNB	75W PAR30L, 65W BR30, 75W R30
E7ICATNB		75W PAR30S, 75W PAR30L, 65W BR30
H27ICAT	H27RICAT	75W PAR30L, 65W BR30, 75W R30
E27ICAT	E27RICAT	75W PAR30L, 65W BR30
H7T	H7RT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
H7TCP		75W PAR30S, 75W R30, 65W BR30
E7TAT		75W PAR30S, 75W PAR30L, 65W BR30
E7RTAT		50W PAR30S, 75W PAR30L, 65W BR30
H7TNB		75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
E7TATNB		75W PAR30S, 75W PAR30L, 65W BR30
H645IC		65W BR30, 75W R30, 75W PAR30L
H27T		75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
H27RT		75W R30
E27TAT	E27RTAT	75W PAR30S, 75W PAR30L, 65W BR30

Compatible with Halogen, Incandescent, LED\* or CFL\* lamps.



**78P**  
White Trim, White Eyeball



**78PAT**  
White Air-Tite™ Trim, White Eyeball



**78SN**  
Satin Nickel Trim, Satin Nickel Eyeball



**78TBZ**  
Tuscan Bronze Trim, Tuscan Bronze Eyeball

### ORDERING INFORMATION

SAMPLE NUMBER: 78P

Trim	Finish
78P= 6" White Eyeball, White Trim	WH=White Trim
78PAT= 6" White Eyeball, White Trim	WH=White Trim
78SN= 6" Satin Nickel Eyeball, Satin Nickel Trim	SN=Satin Nickel
78TBZ= 6" Tuscan Bronze Eyeball, Tuscan Bronze Trim	TBZ=Tuscan Bronze

### HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
419P	Adjustable	•	•	•	•	•	•	•	•
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		H27RT	E27TAT	E27RTAT					

For use in select other's housings, refer to U.L. classification list at [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



For use in Halo listed housings.



Select trims are classified for use in others housings. See [www.eaton.com/lighting/legal](http://www.eaton.com/lighting/legal).