



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 8300WMRI Hosp GRD Duplex Recp 20A 125V Mri WH

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | 8300WMRI  |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Extra Heavy-Duty Hospital Grade Mri Duplex Receptacle Back and Side-Wire 20A 125V |
| Weight per unit  | 0.1667 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro  |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 20   |
| connection          | Back and side wire                               |
| Dielectric Strength | Withstands 2000V minimum                         |
| Material            | Nylon  |
| Number of Wires     | 3  |
| Poles               | 2  |
| Voltage             | 125.0 V  |
| Voltage Rating      | 125  |
| Wattage             | Electrical power is expressed in Amps and Volts. |
| Wire Size           | 14 - 10  |

### Dimensions and Weight

|        |       |
|--------|-------|
| Height | 3.281 |
| Width  | .900  |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | HOSP GRD DUPLEX RECP 20A 125V MRI WH  |
| extra long description | P&S 8300WMRI HOSP GRD DUP RECP 20A  |
| Features               | Extra Heavy-Duty Hospital Grade MRI Duplex Receptacle Back and Side-Wire 20A 125V   |
| Long Description       | Extra Heavy-Duty Hospital Grade MRI Duplex Receptacle Back and Side-Wire 20A 125V   |
| Product Type           | Hosp GRD Dup Recp 20A 125V Mri W  |
| Special Features       | Designed expressly for MRI applications. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty one-piece nickel-plated brass mounting strap with integral ground for superior structural integrity and long-term performance. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Easily accessed break-off, line-contact connecting tab for |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007269178         |
| Manufacturers Part Number | 8300-WMRI              |
| UPC                       | 785007269178           |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Residential Switches                            |
| Type                 | Hospital Grade MRI Receptacle, Extra Heavy-Duty |

## Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 100    |
| Weight Per each | 0.1667 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Commercial                              |
| environmental conditions | Flammability: UL94 V2                   |
| Mounting                 | WALL                                    |
| nema rating              | 5-20R                                   |
| standard                 | CULUS, UL498, CSA C22.2 No. 42, FEDSPEC |