ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



86125 TAPE MEASURE 25' SINGLE-HOOK

KLEIN TOOLS

Catalog Number	86125
Manufacturer	KLEIN TOOLS
Description	Non-Magnetic Tape, Steel (Blade) Material, 25 ft (Tape) Length, 2 in Width, 3.313 in Thickness, 1.1 lb
Weight per unit	1.1 (lbs/each)
Product Category	Tools & Testers

Features

Belt Clip	Yes
Overall Height	3.313" (8.4 cm)
Overall Width	2" (5.1 cm)
Tape Length	25' (7.6 m)
Media	Yes

Material, Color, and Finish

Tape Material	STEEL

Dimensions and Weight

Overall Length	3.5" (8.9 cm)

Descriptions

Description	TAPE MEASURE 25' SINGLE-HOOK
Long Description	Klein Tools Tape Measures offer inventive first-rate features derived from jobsite professionals, to make jobs easier and more efficient. A sealed tape brake panel is large enough to allow 2-3 fingers to operate at once for safe retraction, and keeps water and dirt out to prevent tape blade rust and degradation. The high impact rugged, rubberized industrial design of this non-magnetic single-hook tape offers a good grip and stands up to basic demands of the jobsite.
Product Type	25 Foot Non-Magnetic Tape Measure
Special Features	Uncluttered, easy to read bold lines every 1/8"
Extra Long Description	KLE 86125 25 Foot Non-Magnetic Tape

Manufacturer Information

GTIN	00092644861253
UPC	783523

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS

Availability

Status	Inactive

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	1
Package	6
Weight	17.6
Weight Per Each	1.1 (lbs/each)



Tape Measure Holders



TAPE MEASURES

Cat. No.	UPC 0-92644+	Description
86125	86125-3	25 Ft. Single Hook Tape Measure (Non-Magnetic)
86216	86216-8	16 Ft. Double Hook Magnetic Tape Measure
86225	86225-0	25 Ft. Double Hook Magnetic Tape Measure
86230	86230-4	30 Ft. Double Hook Magnetic Tape Measure
86315	86315-8	5m Double Hook Magnetic Tape Measure - Metric
86375	86375-2	7.5m Double Hook Magnetic Tape Measure - Metric

TAPE MEASURE HOLDERS

Tape Measure	Holder Cat. No.	UPC 0-92644+	Description
86216, 86315	5195	55078-2	Medium Leather Pouch
	5707	55167-3	Nylon Tape Measure Clip/Holder
86125, 86225, 86375	5196	55092-8	Large Leather Pouch
	5707	55167-3	Nylon Tape Measure Clip/Holder
	5195TT	55537-4	Tape Measure Holder With Ring
86230	5196	55092-8	Large Leather Pouch
	5707	55167-3	Nylon Tape Measure Clip/Holder
	5712	55131-4	Nylon Pouch

KLEIN TOOLS®
For Professionals... Since 1857™

See our complete line of **Tools and Tapes**
www.kleintools.com


© 2017 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
Rev. 10/17 **96509**

FIND YOUR LINE™

Klein's innovative markings and rugged rubberized industrial design measures up to any task the jobsite demands!



TAPE MEASURES




Up to
9-1/2 FT. (3m)
STAND-OUT

Patent Pending


UNCLUTTERED, EASY-TO-READ **BOLD LINES EVERY 1/8"**

EXTRA-LARGE BOLD NUMBERS
FOR IMPROVED READABILITY



DOUBLE SIDED BLADES
for multiple viewing positions*

RETRACTION SPEED BRAKE
CONTROLS BLADE SPEED AND PROTECTS FINGERS FROM HAVING TO TOUCH BLADE



MAGNETIC END HOOKS
WITH DUAL ANGLE POLARITY
attaches to conduit and steel studs to easily read from above or below*

SUPER-SIZED POCKET CLIP
holds securely to wide belts and extends deep into pockets

HEAVY-DUTY NYLON COATING
protects printing on blades



Blade-printed Conduit Multiplier
BENDING TABLE
helps calculate offsets & saddles

*Does not apply to #86125, Single Hook Tape Measure



