



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 863.54CHC Encl 8X6X3.5 N4 CH Clamp CVR

*Cooper B-Line/Cable Tray*

Catalog Number	863.54CHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 8" Height, 3.5" Length, 6" Width, Nema 4, Hinged Cover, 4CHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	4.5 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

dimensions	3.5000 IN X 6.0000 IN X 8.0000 IN
Material	Carbon Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	6.00 In Width X 3.50 In Depth X 8.00 In Height
------	--

### Descriptions

Description	ENCL 8X6X3.5 N4 CH CLAMP CVR
extra long description	B-LINE 863.5-4CHC TYPE 4 JIC CONTIN
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 8" height, 3.5" length, 6" width, NEMA 4, Hinged cover, 4CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 4 Jic Continuous Hinge CVR Enc, 8X6X35
Special Features	Cont. piano hinge with s.s. door clamp, panel mount

### Manufacturer Information

Brand	Eaton
GTIN	00782051740301
Manufacturers Part Number	863.5-4CHC
UPC	782051740301

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	4.54

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Critical PowerCommercial / Institutional Buildings / Structures - Critical PowerInd Facilities & Factories - Facility: Automation and MonitoringCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Institutional Buildings / Structures - Power Distribution and ControlsInd Facilities & Factories - Industrial Facilities/Factories - OtherInd Facilities & Factories - Facility: Lighting and Lighting ControlsInd Facilities & Factories
Mounting	EXTERNAL FEET, WALL
standard	UL 50,CSA C22.2.,NEMA