



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



88030 PT1L Led Lithium Flashlight

Streamlight, Inc.

Catalog Number	88030
Manufacturer	Streamlight, Inc.
Description	Tactical Light, Non-Rechargeable, Ultra Compact Type; Black Color; Ce Approval; Machined Anodized Aluminum Body Material; Led Lamp Type; CR123A Battery Size; 1 Battery(S); Yes Battery Included; Protac[R] Brand; Rohs Compliant; Battery Type 3 Volt Lithium
Weight per unit	0.2700 (lbs/each)
Product Category	Flashlights, Lanterns, Warning

Features

Battery Included	Yes
Battery Size	CR123A
Lamp Type	LED
Number of Batteries	1

Material, Color, and Finish

Body Material	Machined Anodized Aluminum
Color	Black



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	RoHS Compliant; Battery Type 3 Volt Lithium; Size 0.9 Inch Diameter x 3.43 Inch Length; Barrel Diameter 0.77 Inch; Initial Intensity 22 to 275 Lumen; Light Output 420 to 5100 Candela; Range of Light/Distance 143 Meter; Runtime 2 to 24 Hour; Enclosure Type
Commodity Description	FLASHLIGHTS, LANTERNS, WARNING LIGHTS
Description	PT1L LED LITHIUM FLASHLIGHT
extra long description	ULTRA COMPACT, NON-RECHARGEABLE TYPE; BLACK COLOR; CE APPROVAL; MACHINED ANODIZED ALUMINUM BODY MATERIAL; LED LAMP TYPE; CR123A BATTERY SIZE; 1 BATTERY(S); YES BATTERY INCLUDED; PROTAC[R] BRAND; ROHS COMPLIANT; BATTERY TYPE 3 VOLT LITHIUM; SIZE 0.9 INCH DIAMETER X 3.43 INCH LENGTH; BARREL DIAMETER 0.77 INCH; INITIAL INTENSITY 22 TO 275 LUMEN; LIGHT OUTPUT 420 TO 5100 CANDELA; RANGE OF LIGHT/DISTANCE 143 METER; RUNTIME 2 TO 24 HOUR; ENCLOSURE TYPE IPX7; INCLUDES TEMPERED GLASS LENS, SEALED O-RING, NYLON HOL
Long Description	TACTICAL LIGHT, NON-RECHARGEABLE, ULTRA COMPACT TYPE; BLACK COLOR; CE APPROVAL; MACHINED ANODIZED ALUMINUM BODY MATERIAL; LED LAMP TYPE; CR123A BATTERY SIZE; 1 BATTERY(S); YES BATTERY INCLUDED; PROTAC[R] BRAND; ROHS COMPLIANT; BATTERY TYPE 3 VOLT LITHIUM
Product Type	Tactical Light

Manufacturer Information

Brand	Streamlight, Inc.
Manufacturers Part Number	88030

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Non-Rechargeable, Ultra Compact

Packaging

Carton	1
Weight Per each	0.27

Uses, Certifications, and Standards

Approval	CE
----------	----